

## RS Stock No : 415-935

002211001 D01 gG 2A/400V



Add to cart



### Specifications

ETI Code	002211001
Description	D01 gG 2A/400V
Weight	5.9
Level	Fuse links gG
Breaking capacity (AC)	50kA
Breaking capacity DC	8kA
Characteristics	gG
Dimensions	E14
Product group	D0 low voltage Fuses
Rated AC voltage	400V
Rated current	2A
Rated DC voltage	250V
Size	D01
Type	D0

## RS Stock No : 415-941

002211002 D01 gG 4A/400V



Add to cart



### Specifications

ETI Code	002211002
Description	D01 gG 4A/400V
Weight	5.9
Level	Fuse links gG
Breaking capacity (AC)	50kA
Breaking capacity DC	8kA
Characteristics	gG
Dimensions	E14
Product group	D0 low voltage Fuses
Rated AC voltage	400V
Rated current	4A
Rated DC voltage	250V
Size	D01
Type	D0

## RS Stock No : 415-957

002211003 D01 gG 6A/400V



Add to cart



### Specifications

ETI Code	002211003
Description	D01 gG 6A/400V
Weight	5.9
Level	Fuse links gG
Breaking capacity (AC)	50kA
Breaking capacity DC	8kA
Characteristics	gG
Dimensions	E14
Product group	D0 low voltage Fuses
Rated AC voltage	400V
Rated current	6A
Rated DC voltage	250V
Size	D01
Type	D0

## RS Stock No : 415-963

002211004 D01 gG 10A/400V



Add to cart



### Specifications

ETI Code	002211004
Description	D01 gG 10A/400V
Weight	6.6
Level	Fuse links gG
Breaking capacity (AC)	50kA
Breaking capacity DC	8kA
Characteristics	gG
Dimensions	E14
Product group	D0 low voltage Fuses
Rated AC voltage	400V
Rated current	10A
Rated DC voltage	250V
Size	D01
Type	D0

## RS Stock No : 415-979

002211005 D01 gG 16A/400V



Add to cart



### Specifications

ETI Code	002211005
Description	D01 gG 16A/400V
Weight	6.6
Level	Fuse links gG
Breaking capacity (AC)	50kA
Breaking capacity DC	8kA
Characteristics	gG
Dimensions	E14
Product group	D0 low voltage Fuses
Rated AC voltage	400V
Rated current	16A
Rated DC voltage	250V
Size	D01
Type	D0

## RS Stock No : 289-8792

002221011 D01 E14 16A N-K 1p



Add to cart



### Specifications

ETI Code	002221011
Description	D01 E14 16A N-K 1p
Weight	.072
Level	Fuse bases
Dimensions	E14
Product group	LV-fuse base
Rated current	16A
Size	D0
Type	D01N-K

# RS Stock No : 289-8815

002231003 KN D01



Add to cart



## Specifications

<i>ETI Code</i>	<b>002231003</b>
<i>Description</i>	<b>KN D01</b>
<i>Weight</i>	<b>.019</b>
<i>Level</i>	<b>Fuse bases and disconnectors</b>
<i>Product group accessories</i>	<b>Fuse Base D0</b>
<i>To use with</i>	<b>Fuse carrier D0</b>
<i>Type accessories</i>	<b>Fuse carrier D0</b>