



### Cable Installation System - Cable Scout+

#### Cable Scout+ Rod Sets

Cable Scout+ is a professional cable routing tool which enables installers to easily route cables, saving time, even with the most challenging installations. The rods are manufactured from high quality Glass Reinforced Plastic (GRP), which enables a load carrying capacity of up to 200 kg. Cable Scout+ offers a range of features which allows the installer to illuminate, grip, inspect and retrieve by using the range of accessories. Cable Scout+ is supplied in a useful durable bag which contains the rods and accessories all in one place.

#### Features and Benefits

- Professional cable installation tool
- Enables time savings to be achieved even with challenging installations
- Rods manufactured from high quality Glass Reinforced Plastic (GRP)
- Load carrying capacity of 200 kg
- Range of accessories enabling the installer to illuminate, grip inspect and retrieve.
- Rods & accessories contained in a useful durable storage bag



Application video: Cable Scout+



All components stored neat and tidy with the Cable Scout+ Deluxe set.



Basic Set.



Handy Set.

TYPE	Description	Content Rods	Rod Capacity (m)	Content Accessories	Article-No.
CS-SB	Basic Set: designed to perform basic cable installation	10 rods x 1 m (white)	10.0 m	15 cm white flexi lead, gender changer, tuff hook, mini eye	897-90000
CS-SD	Deluxe Set: the most comprehensive set aimed for carrying out larger installations	2 rods x 1 m (white) 6 rods x 1 m (red) 2 rods x 1 m (blue)	10.0 m	15 cm white flexi lead, split ring, gender changer, tuff hook, mini eye, domed bullet, flat bullet, beam, single magnet	897-90001
CS-SH	Handy Set: made up for fitting in a tool box	1 rod x 40 cm (white) 2 rods x 40 cm (red) 1 rod x 40 cm (blue)	1.6 m	40 cm white flexi lead, domed bullet, mini hook, mini eye	897-90003

Subject to technical changes.


#### Cable Scout+ Rod Pairs




Overview of the rods selection.

TYPE	Content Rods	Flexibility	Ø D	Article-No.
CS-P6	One pair of 1 m blue rods	strong	6.0	897-90007
CS-PN	One pair of 1 m nylon rods	fully flexible	5.0	897-90008
CS-P5	One pair of 1 m red rods	medium	5.0	897-90006
CS-P4	One pair of 1 m white rods	flexible	4.0	897-90005

All dimensions in mm. Subject to technical changes.



Overview on Cable Scout+ marginal bending radii.



### Cable Installation System - Cable Scout+

#### Cable Scout+ Accessories


Cable Scout+ is supplied with a range of useful standard accessories. Additional accessories can be purchased separately. Cable Grips are designed to grip objects and provide reliable and time saving method of securing cables & pipes to the rods. Just open the grip by compressing the braid, push the grip over the cable or pipe and release the grip, which will contract and establish a tight grip on the cable or pipe to the rod set.

#### Features and Benefits

- Accessory kit includes a lot of useful tools
- User can inspect, illuminate and retrieve
- Cable grips allows a very fast way to pull cables
- Whisk glides smoothly over obstacles
- LED Beam brings light into the dark
- Strong magnet lifts metallic tools up to 2.5 kg weight



Cable Grips are available in five different sizes to attach a wide range of cable diameters.



The Cable Scout+ Beam - a perfect tool for seeing into cavities.



The whisk allows the rod to glide over obstructions easily.



The strong magnet lifts a metallic tool of up to 2.5 kg.

TYPE	Drawing	Description	Article-No.
CS-SA		Accessory Kit: Includes a 15 cm long flexi lead, gender changer, mini hook, tuff hook, mini eye, split ring, round bullet, flat bullet, single magnet, chain	897-90004
CS-ACG1630		Cable Grip: Suitable for diameter 1.6 - 3.0 cm	897-90027
CS-ACG0415		Cable grips: Suitable for diameters 0.4 - 1.5 cm	897-90026
CS-AW		Whisk: Enables cables to glide over rough and uneven surfaces.	897-90018
CS-AB		Beam: Useful LED torch enables inspection of working area. Uses 1 x AAA Battery.	897-90016
CS-AMG2		Strong Magnet: Enables positioning or retrieval of items weighing up to 2.5 kg.	897-90015

Subject to technical changes.