





Noise Filter Part Numbering



Power Supply Series	N/F Input Current	On-board Type		DC Input Standard	Power Supply Series	N/F Input Current	On-board Type		DC Input Standard
		Standard	High Volt Pulse Noise				Standard	High Volt Pulse Noise	
CC1R5-03**-E	1	RSEG-2001	RSAG-2001	-	PAE50S24	4	RSEG-2004	RSAG-2004	-
CC1R5-05**-E	1	RSEG-2001	RSAG-2001	-	PAE50S48	2	RSEG-2002	RSAG-2002	-
CC1R5-12**-E	0.5	RSEG-20R5	RSAG-20R5	-	PAE100S48	4	RSEG-2004	RSAG-2004	-
CC1R5-24**-E	0.5	RSEG-20R5	RSAG-20R5	-	PAF500F24	40	-	-	RDEN-048050
CC1R5-48**-E	0.5	RSEG-20R5	RSAG-20R5	-	PAF600F24	50	-	-	RDEN-048050
CC3-03**-E	2	RSEG-2002	RSAG-2002	-	PAF500F48	20	PAN4820	-	-
CC3-05**-E	2	RSEG-2002	RSAG-2002	-	PAF600F48	30	-	-	RDEN-048050
CC3-12**-E	0.5	RSEG-20R5	RSAG-20R5	-	KWD5	0.5	RSEG-20R5	RSAG-20R5	-
CC3-24**-E	0.5	RSEG-20R5	RSAG-20R5	-	KWD10	0.5	RSEG-20R5	RSAG-20R5	-
CC3-48**-E	0.5	RSEG-20R5	RSAG-20R5	-	KWD15	1	RSEG-2001	RSAG-2001	-
CC6-03**-E	3	RSEG-2003	RSAG-2003	-	KS5	0.5	RSEG-20R5	RSAG-20R5	-
CC6-05**-E	2	RSEG-2002	RSAG-2002	-	KS10	0.5	RSEG-20R5	RSAG-20R5	-
CC6-12**-E	1	RSEG-2001	RSAG-2001	-	KS15	1	RSEG-2001	RSAG-2001	-
CC6-24**-E	0.5	RSEG-20R5	RSAG-20R5	-	KWS5A	1	RSEG-2001	RSAG-2001	-
CC6-48**-E	0.5	RSEG-20R5	RSAG-20R5	-	KWS10A	1	RSEG-2001	RSAG-2001	-
CC10-05**-E	4	RSEG-2004	RSAG-2004	-	KWS15A	1	RSEG-2001	RSAG-2001	-
CC10-12**-E	2	RSEG-2002	RSAG-2002	-	KWS25A	1	RSEG-2001	RSAG-2001	-
CC10-24**-E	1	RSEG-2001	RSAG-2001	-	KWS5	0.5	RSEG-20R5	RSAG-20R5	-
CC10-48**-E	0.5	RSEG-20R5	RSAG-20R5	-	KWS10	0.5	RSEG-20R5	RSAG-20R5	-
CC15-24**-E	2	RSEG-2002	RSAG-2002	-	KWS15	1	RSEG-2001	RSAG-2001	-
CC25-24**-E	2	RSEG-2002	RSAG-2002	-	PAF700F48	30	-	-	RDEN-048050
CC15-24**P-E	2	RSEG-2002	RSAG-2002	-	PAF450F280	4	RSEG-2004	RSAG-2004	-
CC15-48**P-E	1	RSEG-2001	RSAG-2001	-	PAF600F280	6	RSEG-2006	RSAG-2006	-
CC30-24**P-E	3	RSEG-2003	RSAG-2003	-	PAH300S24	16	PAN4820	-	-
CC30-48**P-E	2	RSEG-2002	RSAG-2002	-	PAH350S24	16	PAN4820	-	-
CCG30-24	6	RSEG-2006	RSAG-2006	-	PAH50S48	1	RSEG-2001	RSAG-2001	-
CCG30-48	3	RSEG-2003	RSAG-2003	-	PAH75S48	2	RSEG-2002	RSAG-2002	-
CN30A110	1	RSEG-2001	RSAG-2001	-	PAH100S48	2	RSEG-2002	RSAG-2002	-
CN50A110	2	RSEG-2002	RSAG-2002	-	PAH150S48	3	RSEG-2003	RSAG-2003	-
CN100A110	3	RSEG-2003	RSAG-2003	-	PAH200S48	4	RSEG-2004	RSAG-2004	-
CN200A110	6	RSEG-2006	RSAG-2006	-	PAH300S48	6	RSEG-2006	RSAG-2006	-
CN50A24	6	RSEG-2006	RSAG-2006	-	PAH350S48	10	PAN4820	-	-
CN100A24	10	PAN4820	-	-	PAH450S48	10	PAN4820	-	-
iEA	6	RSEG-2006	RSAG-2006	-	PAH75D24	4	RSEG-2004	RSAG-2004	-
iEE	4	RSEG-2004	RSAG-2004	-	PAH75D48	2	RSEG-2002	RSAG-2002	-
iQE	16	PAN4820	-	-	PAH200H	4	RSEG-2004	RSAG-2004	-
iQL	20	PAN4820	-	-	PAQ50S48	1	RSEG-2001	RSAG-2001	-
iQG	16	PAN4820	-	-	PAQ100S48	2	RSEG-2002	RSAG-2002	-
KWS15	6	RSEG-2006	RSAG-2006	-	PAQ65D	2	RSEG-2002	RSAG-2002	-
KWD5	0.5	RSEG-20R5	RSAG-20R5	-	PF500A	10	PAN4820	-	-
KWD10	1	RSEG-2001	RSAG-2001	-	PF1000A	16	PAN4820	-	-
KWD15	1	RSEG-2001	RSAG-2001	-	PFE300SA	6	RSEG-2006	RSAG-2006	-
PAE50S24	4	RSEG-2004	RSAG-2004	-	PFE500SA	10	PAN4820	-	-
PAE50S48	2	RSEG-2002	RSAG-2002	-	PFE700SA	16	PAN4820	-	-
PAE100S48	4	RSEG-2004	RSAG-2004	-	PFE500F	10	PAN4820	-	-
PAF500F24	40	-	-	RDEN-048050	PFE1000F	20	PAN4820	-	-
PAF600F24	50	-	-	RDEN-048050	PH50A280	0.5	RSEG-20R5	RSAG-20R5	-
PAF500F48	20	PAN4820	-	-	PH75A280	0.5	RSEG-20R5	RSAG-20R5	-
PAF600F48	30	-	-	RDEN-048050	PH100A280	0.5	RSEG-20R5	RSAG-20R5	-
CN50A24	6	RSEG-2006	RSAG-2006	-	PH150A280	0.5	RSEG-20R5	RSAG-20R5	-
CN100A24	10	PAN4820	-	-					
iEA	6	RSEG-2006	RSAG-2006	-					
iEE	4	RSEG-2004	RSAG-2004	-					
iQE	16	PAN4820	-	-					
iQL	20	PAN4820	-	-					
iQG	16	PAN4820	-	-					