



**3 YEAR
WARRANTY**



Data sheet

RS PRO Dual Channel Soldering Station, 130 W Soldering Iron and 100 W Tweezers

Stock number: 176-0007

EN



Specifications

Model	176-0007
Power consumption	200 W (MAX)
Input voltage	230 V ac \pm 10% 50 Hz
Temperature range	150 - 480°C (302 - 896°F)
Stand-by mode	Support
Shortcut Temperature	3 groups temperatures can adjust and use quickly
Auto-sleep mode	Support
Dimensions	L265 x W230 x H160 mm
Net weight	4.97 kg

Features


- The two channels can work simultaneously (soldering iron and the tweezers)
- Large LCD display illustrate supporting parameter data
- Soldering station will automatically recognise the soldering tools that you connect and upload the corresponding parameters
- To support simplified operations there are three pre-set temperature operations
- Maximum power output for the single channel soldering iron is 150w (ability to support welding large bond pads and weldments)
- The soldering station combined maximum power output is 200w
- 100w soldering tweezers allow soldering and desoldering various SMD devices
- The soldering iron can reach maximum temperature within 10 seconds

Packing List













176-0007 Main Unit	1pc	
GT-Y130 Soldering Iron	1pc	
GT-N100 Tweezers	1pc	
Iron holder (with Cleaning Sponge)	2sets	
Manual	2 copies	
Power Cord(UK + European Plug)	2pc	
3.5MM Grounding Receptacle	1pc	

Replacement Accessories



















Soldering Iron and Tweezers

SKU	Description
1790020 	50W Soldering Iron for 176-0007
1790021 	130W Soldering Iron for 176-0007
1790022 	150W Soldering Iron for 176-0007
1790023 	100W Tweezers for 176-0007













Replacement Tweezers for 179-0023 - 100W Tweezers

1796031 	Replacement tweezers for 1790023			
1796032 	Replacement tweezers for 1790023			
1796033 	Replacement tweezers for 1790023			

Replacement Tip for 179-0021 - 130W Soldering Iron

1796035	Replacement tip for 1790021		
1796036	Replacement tip for 1790021		
1796037	Replacement tip for 1790021		
1796038	Replacement tip for 1790021		
1796039	Replacement tip for 1790021		
1796040	Replacement tip for 1790021		
1796041	Replacement tip for 1790021		
1796042	Replacement tip for 1790021		
1796043	Replacement tip for 1790021		

Replacement Tip for 179-0022 - 150W Soldering Iron

1796044	Replacement tip for 1790022		
1796045	Replacement tip for 1790022		
1796046	Replacement tip for 1790022		
1796047	Replacement tip for 1790022		
1796048	Replacement tip for 1790022		
1796049	Replacement tip for 1790022		
1796050	Replacement tip for 1790022	