

ELARA350



"SERVICES" FALL ARRESTER SET : HAR24 + AN060 + AN315 + EX021 + 2 AM002 + LV102100 + HA200

Ref. ELARA350_



Product specifications

SERVICES - ready for use fall arrester kit: Harness with extensible "Riplight System II®" patented waves with positioning belt. 2 fall arrester anchorage points (back - front). 4 adjustable buckles. Positioning belt with thermoformed back closed with wide Velcro. 120° rotation. 2 lateral anchorage points for work positioning (ref. HAR24). Fall arrester sliding on anchorage line stranded rope Ø 14 mm, opening type, equipped with automatic locking, non-inverting device, energy absorber with fall indicator (ref. AN060). Anchorage line stranded rope Ø 14 mm (ref. AN315). Adjustable work positioning lanyard via reducer. Adjustable length. Stranded rope Ø 12 mm. Protective sheath on the splices (ref. EX021). Anchorage ring with high tenacity polyester strap. Width 45 mm. End loop with shrinkage and steel anchor D (ref. LV102100). 1 tool holder (ref. HA200). 2 carabiners AM002.

Fall arrest harness with positioning belt. Polyester straps.

Fall protection slide on supporting belay: Galvanized steel. Polyamide rope.

Carabiner: Steel.

COLOUR

Black-Orange

SIZE

S/M/L, XL/XXL

Product Use - Risks



Fall



Construction / Civil engineering



Second work / craftman



Light industry



Services / Logistics



Short vertical movement or movement on inclined surface (less than 3 m)



Short horizontal

movement (less than 3 m)



Long vertical movement or movement on inclined surface



Long

horizontal movement on horizontal surface
Restraint



Long horizontal movement on vertical structure



Product's highlights & user's benefits



Certifications and Standards



PPE DIRECTIVE 89/686/EEC

EN363 : 2008 Personal fall protection equipment - Personal fall protection systems

EN364 : 1992 Personal fall protection equipment : Test method

EN365 : 2004 General requirements for the instructions for use and the marking

EN353-2 : 2002 Personal protection equipment against falls from a height - Part 2 : Guided type fall arresters on a flexible anchor line.



EN361 : 2002 Personal protection equipment against falls from a height - Full body harnesses

EN358 : 1999 Personal fall protection equipment for work positioning and prevention of falls from a height - Belts for work positioning and restraint and work positioning lanyards.

EN795:2012 Personal fall protection equipment : Anchorage devices
TYPE B: Anchorage device type B

EN362 : 2004 Personal protection equipment against falls from a height - Connectors

References

References	Bar code	COLOUR	SIZE		
ELARA350GT	3295249201623	Black-Orange	S/M/L	3	-
ELARA350XX	3295249201647	Black-Orange	XL/XXL	3	-