

Flat-Screen TV Wall Mount - Tilting

Product ID: FLATPNLWALL



Maximize space while creating an impressive display with this flat-screen TV wall mount for large TVs or monitors. The heavy-duty wall mount securely supports a VESA Mount compliant TV from 32" to 75", with easy-to-use tilt adjustment for comfortable viewing.



Ideal for the Boardroom, or Digital Signage

Mount your flat-screen TV in a location that's convenient for visitors, clients and employees, while saving valuable space. The wall mount is ideal for boardrooms, lobbies or other venues providing an impressive and secure way to display a large flat-panel TV or create digital signage. The robust wall mount supports a large 32" to 75" flat-screen TV weighing up to 165 lb. (75 kg).

Tilt Your Display to the Ideal Viewing Angle

The TV wall mount lets you angle your TV display toward your audience. With the tilt feature, you can mount your TV lower or higher than eye level and still view it comfortably. The tilt-adjusting knobs make it easy to adjust your TV to the ideal viewing angle.



Easy and Secure Setup

The hook-and-mount design of the TV wall mount makes setup fast and easy. You simply attach the vertical brackets, with built-in hooks, to the back of your TV. Once the brackets are attached, you then hang your TV securely onto the wall mount. Cable management helps to keep cables out of view.

The FLATPNLWALL is backed by a StarTech.com 5-year warranty and free lifetime technical support.

**Certifications, Reports
and Compatibility**



Applications

- Safely and securely wall-mount your TV
- Keep guests informed and entertained
- Ideal for lobbies, lecture halls, classrooms and meeting spaces
- Save space in your home theater or living room

Features

- Save space with this flat screen wall mount for 32" to 75" TVs
- Tilt your TV up or down (+15 to -15 degrees) for comfortable viewing
- Heavy-duty steel TV wall mount supports up to 165 lb. (75 kg)
- Fits curved TVs, with compatible VESA mount
- Hook-and-mount design for easy setup with VESA compliant TVs

Hardware	Warranty	5 Years
	# of Displays Supported	1
	Mounting Options	Wall-Mount
	VESA Hole Pattern(s)	200x200 mm
		300x300 mm
		400x200 mm
		400x400 mm
600x400 mm		
700x400 mm		
Wallmountable	Yes	
Performance	Anti-theft	No
	Fits Curved TV	Yes
	Maximum Display Size	75"
	Minimum Display Size	32"
	Tilt	+ 15° / - 15°
	Video Wall	No
	Weight Capacity (Per Display)	165.8 lb [75 kg]
Physical Characteristics	Color	Black
	Internal Depth	3.3 in [83 mm]
	Internal Height	19.7 in [500 mm]
	Internal Width	31.9 in [810 mm]
	Product Height	19.7 in [500 mm]
	Product Length	31.9 in [810 mm]
	Product Weight	8.5 lb [3.8 kg]
	Product Width	3.3 in [83 mm]
Packaging Information	Shipping (Package) Weight	10.7 lb [4.9 kg]
What's in the Box	Included in Package	1 - wall plate
		1 - left bracket
		1 - right bracket
		1 - Allen key

- 4 - M5x14 mm screws
- 4 - M6x14 mm screws
- 4 - M8x30 mm screws
- 4 - M6x30 mm screws
- 4 - M8x50 mm screws
- 4 - washers
- 8 - short spacers
- 8 - long spacers
- 6 - 6.3x55 mm screws
- 6 - concrete anchors
- 6 - flat washers
- 1 - instruction manual

Product appearance and specifications are subject to change without notice.