

## Range box - AI SORTI BOX ANT - 3202973

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Sorti-box, equipped with ferrules in accordance with DIN 46228-4, CSA-certified, 50 pcs. of AI 4-10 GY, 20 pcs. each of AI 6-12 YE, AI 10-12 RD, 10 pcs. of AI 16-12 BU

### Your advantages

- ✓ Color coding and the transparent cover facilitate fast access to the required ferrules
- ✓ The practical assortment boxes are designed to keep your workshop tidy
- ✓ Using the integrated euro-clip, they can be hung up on perforated board walls, for example, to save space

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 947118
GTIN	4017918947118
Weight per Piece (excluding packing)	113.120 g
Custom tariff number	85369010
Country of origin	Germany

### Technical data

#### Ambient conditions

Short-term temperature	120 °C
Max. permanent temperature	105 °C (-40°C no load / 0°C dynamic load)

#### General

Color	anthracite
Components	free from silicone and halogen
Flammability rating according to UL 94	HB
Material	CU-DHP
Coating	tin-plated (galvanic)

### Standards and Regulations

# Range box - AI SORTI BOX ANT - 3202973

## Technical data

### Standards and Regulations

Connection in acc. with standard	CSA
Flammability rating according to UL 94	HB

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Articles in set

Ferrule - AI 4 -10 GY - 3200535



Ferrule, sleeve length: 10 mm, length: 17 mm, color: gray

Ferrule - AI 6 -12 YE - 3200548



Ferrule, sleeve length: 12 mm, length: 20 mm, color: yellow

Ferrule - AI 10 -12 RD - 3200551



Ferrule, sleeve length: 12 mm, length: 22 mm, color: red

Ferrule - AI 16 -12 BU - 3200564



Ferrule, sleeve length: 12 mm, length: 24 mm, color: blue

# Range box - AI SORTI BOX ANT - 3202973

## Classifications

### eCl@ss

eCl@ss 4.0	27060701
eCl@ss 4.1	27060701
eCl@ss 5.0	27400201
eCl@ss 5.1	27400200
eCl@ss 6.0	27400200
eCl@ss 7.0	27400218
eCl@ss 8.0	27400218
eCl@ss 9.0	27400218

### ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000524
ETIM 6.0	EC000524
ETIM 7.0	EC000524

### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	39121421

## Approvals

### Approvals

---

#### Approvals

CSA / CSAus / cCSAus

---

#### Ex Approvals


---

### Approval details

CSA		<a href="http://www.csagroup.org/services-industries/product-listing/">http://www.csagroup.org/services-industries/product-listing/</a>	247397
-----	--	---	--------

## Range box - AI SORTI BOX ANT - 3202973

### Approvals

CSAus		<a href="http://www.csagroup.org/services-industries/product-listing/">http://www.csagroup.org/services-industries/product-listing/</a>	247397
-------	---	---	--------

cCSAus			
--------	---	--	--