























- Standard hood
- Corrosion-resistant hood (series K)



Side clip on hood

Style	Ordering number	Cable entry			Description	Outline drawing dimensions in mm		
		 PG	 PG	 PG				
<b>Hood</b> side entry standard construction	 	41.32.16.05 41.32.16.79 41.32.16.69	16	16	16	HA.16.STS.1.16 HA.16.STS.1.16.Z HA.16.STS.1.16.G		
		51.41.32.16.05 51.41.32.16.79 51.41.32.16.69	16	16	16			
high construction	 	49.32.25.05 49.32.25.79 49.32.25.69 49.32.25.07 49.32.25.80 49.32.25.70	16	16	16	HD.25.STS.1.16 HD.25.STS.1.16.Z HD.25.STS.1.16.G HD.25.STS.1.21 HD.25.STS.1.21.Z HD.25.STS.1.21.G		
		51.49.32.25.05 51.49.32.25.79 51.49.32.25.69 51.49.32.25.07 51.49.32.25.80 51.49.32.25.70	16	16	16			
top entry standard construction	 	41.30.16.05 41.30.16.79 41.30.16.69	16	16	16	HA.16.STO.1.16 HA.16.STO.1.16.Z HA.16.STO.1.16.G		
		51.41.30.16.05 51.41.30.16.79 51.41.30.16.69	16	16	16			
high construction	 	49.30.25.05 49.30.25.79 49.30.25.69 49.30.25.07 49.30.25.80 49.30.25.70	16	16	16	HD.25.STO.1.16 HD.25.STO.1.16.Z HD.25.STO.1.16.G HD.25.STO.1.21 HD.25.STO.1.21.Z HD.25.STO.1.21.G		
		51.49.30.25.05 51.49.30.25.79 51.49.30.25.69 51.49.30.25.07 51.49.30.25.80 51.49.30.25.70	16	16	16			