





















- Standard hood
- Corrosion-resistant hood (series K)



Locking bayonet on hood

Style	Ordering number	Cable entry			Description	Outline drawing dimensions in mm	
		 PG	 PG	 PG			
Hood side entry standard construction  	42.32.16.07 42.32.16.80 42.32.16.70	21	21	21	HB.16.STS.1.21 HB.16.STS.1.21.Z HB.16.STS.1.21.G	 	
	51.42.32.16.07 51.42.32.16.80 51.42.32.16.70	21	21	21	HB-K.16.STS.1.21 HB-K.16.STS.1.21.Z HB-K.16.STS.1.21.G		
high construction  	49.32.40.07 49.32.40.80 49.32.40.70 49.32.40.09 49.32.40.81 49.32.40.71	21	21	21	HD.40.STS.1.21 HD.40.STS.1.21.Z HD.40.STS.1.21.G HD.40.STS.1.29 HD.40.STS.1.29.Z HD.40.STS.1.29.G	 	
	51.49.32.40.07 51.49.32.40.80 51.49.32.40.70 51.49.32.40.09 51.49.32.40.81 51.49.32.40.71	21	21	29	29		HD-K.40.STS.1.21 HD-K.40.STS.1.21.Z HD-K.40.STS.1.21.G HD-K.40.STS.1.29 HD-K.40.STS.1.29.Z HD-K.40.STS.1.29.G
top entry standard construction  	42.30.16.07 42.30.16.80 42.30.16.70	21	21	21	HB.16.STO.1.21 HB.16.STO.1.21.Z HB.16.STO.1.21.G	 	
	51.42.30.16.07 51.42.30.16.80 51.42.30.16.70	21	21	21	21		HB-K.16.STO.1.21 HB-K.16.STO.1.21.Z HB-K.16.STO.1.21.G
high construction  	49.30.40.07 49.30.40.80 49.30.40.70 49.30.40.09 49.30.40.81 49.30.40.71	21	21	21	HD.40.STO.1.21 HD.40.STO.1.21.Z HD.40.STO.1.21.G HD.40.STO.1.29 HD.40.STO.1.29.Z HD.40.STO.1.29.G	 	
	51.49.30.40.07 51.49.30.40.80 51.49.30.40.70 51.49.30.40.09 51.49.30.40.81 51.49.30.40.71	21	21	29	29		HD-K.40.STO.1.21 HD-K.40.STO.1.21.Z HD-K.40.STO.1.21.G HD-K.40.STO.1.29 HD-K.40.STO.1.29.Z HD-K.40.STO.1.29.G