



For more Information  
please call

1-800-Belden1



### General Description:

20 AWG stranded (7x28) TC conductors, polyethylene insulation, twisted pair, overall Beldfoil® shield (100% coverage), 20 AWG stranded TC drain wire, PVC jacket.

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	20	7x28	TC - Tinned Copper

Total Number of Conductors: 2

#### Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PE - Polyethylene	0.017

#### Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape w/Shorting Fold	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
20	7x28	TC - Tinned Copper

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.028

#### Overall Cable

Overall Cabling Lay Length & Direction:

Length (in.)	Direction	Twists (twist/ft)
2.000	Left Hand	6.000

Overall Nominal Diameter: 0.204 in.

#### Pair

Pair Color Code Chart:

Number	Color
1	Black & Clear

### Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +60°C
UL Temperature Rating:	60°C (UL AWM Style 2092)
Bulk Cable Weight:	21 lbs/1000 ft.
Max. Recommended Pulling Tension:	46 lbs.
Min. Bend Radius/Minor Axis:	2.250 in.

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
NEC Articles:	800
CEC/(UL) Specification:	CM
AWM Specification:	UL Style 2092 (300 V 60°C)
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes

**Flame Test**

UL Flame Test:	UL1685 UL Loading
CSA Flame Test:	FT1

**Suitability**

Suitability - Indoor:	Yes
-----------------------	-----

**Plenum/Non-Plenum**

Plenum (Y/N):	No
---------------	----

**Electrical Characteristics (Overall)**

**Nom. Characteristic Impedance:**

**Impedance (Ohm)**

56

**Nom. Inductance:**

**Inductance (µH/ft)**

.18

**Nom. Capacitance Conductor to Conductor:**

**Capacitance (pF/ft)**

27

**Nom. Capacitance Cond. to Other Conductor & Shield:**

**Capacitance (pF/ft)**

49

**Nom. Conductor DC Resistance:**

**DCR @ 20°C (Ohm/1000 ft)**

9.5

**Max. Operating Voltage - UL:**

**Voltage**

300 V RMS

**Max. Recommended Current:**

Description	Current
10C temperature rise	3.9 Amps per conductor @ 25°C ambient

**Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8762 060U1000	1,000 FT	23.000 LB	CHROME		2 #20 PE FS PVC
8762 060U500	500 FT	12.500 LB	CHROME		2 #20 PE FS PVC
8762 060100	100 FT	2.900 LB	CHROME		2 #20 PE FS PVC
8762 0601000	1,000 FT	23.000 LB	CHROME	C	2 #20 PE FS PVC
8762 06010000	10,000 FT	240.000 LB	CHROME	C Y	2 #20 PE FS PVC
8762 0602000	2,000 FT	46.000 LB	CHROME	C	2 #20 PE FS PVC
8762 060250	250 FT	6.250 LB	CHROME		2 #20 PE FS PVC
8762 060500	500 FT	12.000 LB	CHROME	C	2 #20 PE FS PVC

**Notes:**

C = CRATE REEL PUT-UP.

Y = FINAL PUT-UP LENGTH MAY VARY -10% TO +20% FROM LENGTH SHOWN.MAY CONTAIN 2 PIECES. MINIMUM LENGTH OF ANY ONE PIECE IS 1500'.

Revision Number: 2    Revision Date: 08-02-2013

© 2015 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities

## 8762 Multi-Conductor - Single-Pair Cable

and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.