

För icke direkt toleranssatta mått gäller toleransklass  
General tolerances if not otherwise stated




NOM DIM MM		TOL CLASS		
From	To	A	B	C
(1)	6	±0.05	±0.1	±0.2
(6)	30	±0.1	±0.2	±0.5
(30)	100	±0.15	±0.3	±0.8
(100)	300	±0.2	±0.5	±1.2
(300)	1000	±0.3	±0.8	±2

Hål / Holes H13


Skarpa kanter brutna där ej annat anges.  
No sharp edges unless otherwise specified.

Övriga generella toleranser enligt ritning 4100-4644.  
Additional general tolerances in accordance with drawing 4100-4644.

Denna ritning är Pressmaster AB:s egendom. Skyddad av gällande lag.  
This drawing is the property of Pressmaster AB. Protected in accordance with privailing law.



4101-0271




4300-3690

Rev	Change order	Change: A = Added W = Was D = Deleted	Date	Sign
11	P2751	Ändrad enligt kund/ Changed according to the customer	091103	SE

FÖRSPÄNNING / PRELOAD: 150 ± 20 N

Tolkmått / Gauge dimensions (mm)		
URTAG	Gåtolk	Stopptolk
NEST	GO	NO GO
HEX 3.25	∅3.20	∅3.30
HEX 4.52	∅4.47	∅4.57
HEX 1.69	∅1.66	∅1.72

Material		Behandling/Treatment			Status	
Konstr/Design OS		Ritad/Drawn TGW	Datum/Date 2009-11-03	Skala/Scale 1:2	Kontr/Checked IP	Godk/Approved NE
<b>pressmaster</b> <sup>®</sup>  REG NR FM19447				Benämning/Denomination <b>KRIMPTÅNG 298-1080</b> <b>CRIMPING TOOL</b>		Vikt/Weight,gram 43002439
					Årnr/Blank Frisläppt	Art grp 012
					Ritr nr/Drawing no 43002439	REV 007