

Klübertemp GR RT 15

Version 1.4

Revision Date 07.07.2017

Print Date 07.07.2017

1. Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Product name : Klübertemp GR RT 15

Article-No. : 090182

1.2 Relevant identified uses of the substance or mixture and uses advised against

Use of the Substance/Mixture : Lubricant

Recommended restrictions on use : Restricted to professional users.

1.3 Details of the supplier of the safety data sheet

Klüber Lubrication München
Geisenhausenerstr. 7
81379 München
Deutschland
Tel: +49 (0) 89 7876 0
Fax: +49 (0) 89 7876 333
info@klueber.com

E-mail address : mcm@klueber.com
Responsible/issuing person : Material Compliance Management

National contact : Klüber Lubrication Great Britain Limited
Unit 10 Pennine Business Park
Longbow Close
Huddersfield
West Yorkshire HD2 1GQ
Great Britain
Tel: +44-1422-205115
Fax: +44-1422-206073
sales@uk.klueber.com

1.4 Emergency telephone number

+49 89 7876 700 (24 hrs)

2. Hazards identification

2.1 Classification of the substance or mixture

Classification (REGULATION (EC) No 1272/2008)

Not a hazardous substance or mixture.

Classification (67/548/EEC, 1999/45/EC)

Klübertemp GR RT 15

Version 1.4

Revision Date 07.07.2017

Print Date 07.07.2017

Not a hazardous substance or mixture.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

Not a hazardous substance or mixture.

2.3 Other hazards

3. Composition/information on ingredients

3.2 Mixtures

Chemical nature : perfluorinated polyether oil
PTFE

Remarks : No hazardous ingredients

4. First aid measures

4.1 Description of first aid measures

- If inhaled : Remove person to fresh air. If signs/symptoms continue, get medical attention.
Keep patient warm and at rest.
If breathing is irregular or stopped, administer artificial respiration.
- In case of skin contact : Remove contaminated clothing. If irritation develops, get medical attention.
In case of contact, immediately flush skin with plenty of water.
- In case of eye contact : Rinse immediately with plenty of water, also under the eyelids, for at least 10 minutes.
If eye irritation persists, consult a specialist.
- If swallowed : Move the victim to fresh air.
Do not induce vomiting without medical advice.

4.2 Most important symptoms and effects, both acute and delayed

Symptoms : No information available.

Risks : None known.

4.3 Indication of any immediate medical attention and special treatment needed

Treatment : No information available.

5. Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Klübertemp GR RT 15

Version 1.4

Revision Date 07.07.2017

Print Date 07.07.2017

Unsuitable extinguishing media : High volume water jet

5.2 Special hazards arising from the substance or mixture

Specific hazards during firefighting : Fire may cause evolution of:
Carbon oxides
Halogenated compounds

5.3 Advice for firefighters

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus. Use personal protective equipment. In the case of respirable dust and/or fumes, use self-contained breathing apparatus. Exposure to decomposition products may be a hazard to health.

Further information : Standard procedure for chemical fires.

6. Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Evacuate personnel to safe areas. Use the indicated respiratory protection if the occupational exposure limit is exceeded and/or in case of product release (dust). Avoid breathing dust. Refer to protective measures listed in sections 7 and 8.

6.2 Environmental precautions

Environmental precautions : Try to prevent the material from entering drains or water courses. Local authorities should be advised if significant spillages cannot be contained.

6.3 Methods and materials for containment and cleaning up

Methods for cleaning up : Clean up promptly by sweeping or vacuum. Keep in suitable, closed containers for disposal.

6.4 Reference to other sections

For personal protection see section 8.

7. Handling and storage

7.1 Precautions for safe handling

Advice on safe handling : For personal protection see section 8. Smoking, eating and drinking should be prohibited in the application area. Wash hands and face before breaks and immediately after handling the product.

Klübertemp GR RT 15

Version 1.4

Revision Date 07.07.2017

Print Date 07.07.2017

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Store in original container.
Keep container closed when not in use.
Keep in a dry, cool and well-ventilated place.
Containers which are opened must be carefully resealed and kept upright to prevent leakage.
Store in accordance with the particular national regulations.
Keep in properly labelled containers.

7.3 Specific end use(s)

: Consult the technical guidelines for the use of this substance/mixture.

8. Exposure controls/personal protection

8.1 Control parameters

Contains no substances with occupational exposure limit values.

8.2 Exposure controls

Engineering measures

Maintain air concentrations below occupational exposure standards.

Personal protective equipment

Respiratory protection : Not required; except in case of aerosol formation.
Filter type P

Hand protection : For prolonged or repeated contact use protective gloves.
The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it.
The break through time depends amongst other things on the material, the thickness and the type of glove and therefore has to be measured for each case.
In case of contact through splashing:

: Nitrile rubber
Protective index Class 1

Eye protection : Tightly fitting safety goggles

Hygiene measures : Wash face, hands and any exposed skin thoroughly after handling.

Protective measures : The type of protective equipment must be selected according to the concentration and amount of the dangerous substance

Klübertemp GR RT 15

Version 1.4

Revision Date 07.07.2017

Print Date 07.07.2017

at the specific workplace.
Choose body protection in relation to its type, to the concentration and amount of dangerous substances, and to the specific work-place.

Environmental exposure controls

General advice : Try to prevent the material from entering drains or water courses.
Local authorities should be advised if significant spillages cannot be contained.

9. Physical and chemical properties

9.1 Information on basic physical and chemical properties

Form : paste

Colour : white

Odour : odourless

Odour Threshold : No data available

pH : No data available

Melting point/range : No data available

Boiling point/boiling range : No data available

Flash point : does not flash

Evaporation rate : No data available

Flammability (solid, gas) : Will not burn

Lower explosion limit : No data available

Upper explosion limit : No data available

Vapour pressure : < 0.001 hPa, 20 °C

Relative vapour density : No data available

Density : 1.99 g/cm³, 20 °C

Water solubility : insoluble

Solubility in other solvents : No data available

Partition coefficient: n-octanol/water : No data available

Auto-ignition temperature : No data available

Ignition temperature : No data available

Thermal decomposition : No data available

Viscosity, dynamic : No data available

Viscosity, kinematic : No data available

Explosive properties : Not explosive

Oxidizing properties : No data available

Klübertemp GR RT 15

Version 1.4

Revision Date 07.07.2017

Print Date 07.07.2017

9.2 Other information

Sublimation point : No data available
Bulk density : No data available

10. Stability and reactivity

10.1 Reactivity

No hazards to be specially mentioned.

10.2 Chemical stability

Stable under normal conditions.

10.3 Possibility of hazardous reactions

Hazardous reactions : No dangerous reaction known under conditions of normal use.

10.4 Conditions to avoid

Conditions to avoid : No conditions to be specially mentioned.

10.5 Incompatible materials

Materials to avoid : No materials to be especially mentioned.

10.6 Hazardous decomposition products

Hazardous decomposition products : >280 °C danger of forming toxic pyrolysis products.

11. Toxicological information

11.1 Information on toxicological effects

Product

Acute oral toxicity : This information is not available.
Acute inhalation toxicity : This information is not available.
Acute dermal toxicity : This information is not available.
Skin corrosion/irritation : This information is not available.
Serious eye damage/eye irritation : This information is not available.
Respiratory or skin sensitisation : This information is not available.
Germ cell mutagenicity
Genotoxicity in vitro : No data available
Genotoxicity in vivo : No data available
Carcinogenicity : No data available
Reproductive toxicity : No data available
Teratogenicity : No data available

Klübertemp GR RT 15

Version 1.4

Revision Date 07.07.2017

Print Date 07.07.2017

Repeated dose toxicity	:	This information is not available.
Aspiration toxicity	:	This information is not available.
Further information	:	Information given is based on data on the components and the toxicology of similar products.

12. Ecological information

12.1 Toxicity

Product:

Toxicity to fish	:	No data available
Toxicity to daphnia and other aquatic invertebrates	:	No data available
Toxicity to algae	:	No data available
Toxicity to bacteria	:	No data available

12.2 Persistence and degradability

Product:

Biodegradability	:	No data available
Physico-chemical removability	:	No data available

12.3 Bioaccumulative potential

Product:

Bioaccumulation	:	This mixture contains no substance considered to be persistent, bioaccumulating and toxic (PBT)., This mixture contains no substance considered to be very persistent and very bioaccumulating (vPvB).
-----------------	---	--

12.4 Mobility in soil

Product:

Mobility	:	No data available
Distribution among environmental compartments	:	No data available

12.5 Results of PBT and vPvB assessment

Product:

Assessment	:	This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.
------------	---	--

12.6 Other adverse effects

Klübertemp GR RT 15

Version 1.4

Revision Date 07.07.2017

Print Date 07.07.2017

Product:

Additional ecological information : No information on ecology is available.

13. Disposal considerations

13.1 Waste treatment methods

Product : The product should not be allowed to enter drains, water courses or the soil.
: Waste codes should be assigned by the user based on the application for which the product was used.

Contaminated packaging : Empty containers can be landfilled, when in accordance with the local regulations.

14. Transport information

14.1 UN number

ADR

Not dangerous goods

IMDG

Not dangerous goods

IATA

Not dangerous goods

14.2 Proper shipping name

ADR

Not dangerous goods

IMDG

Not dangerous goods

IATA

Not dangerous goods

14.3 Transport hazard class

ADR

Not dangerous goods

IMDG

Not dangerous goods

IATA

Not dangerous goods

14.4 Packing group

ADR

Not dangerous goods

IMDG

Not dangerous goods

IATA

Not dangerous goods

14.5 Environmental hazards

Klübertemp GR RT 15

Version 1.4

Revision Date 07.07.2017

Print Date 07.07.2017

ADR

Not dangerous goods

IMDG

Not dangerous goods

IATA

Not dangerous goods

14.6 Special precautions for user

No special precautions required.

14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Remarks : Not applicable for product as supplied.

15. Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59) : This product does not contain substances of very high concern (Regulation (EC) No 1907/2006 (REACH), Article 57).

Major Accident Hazard Legislation : 2012/18/EU Update: Not applicable

: 96/82/EC Update: Not applicable

Directive 2010/75/EU of 24 November 2010 on industrial emissions (integrated pollution prevention and control) : Volatile organic compounds (VOC) content: 68.1 % VOC content excluding water

15.2 Chemical safety assessment

This information is not available.

16. Other information

Further information

This safety datasheet applies only to products originally packaged and labelled by KLÜBER LUBRICATION. The information contained therein is protected by copyright and must not be reproduced or amended without the express written approval of KLÜBER LUBRICATION. This document may be passed on only to the extent required by law. Any dissemination of our safety datasheets (e.g. as a document for download from the Internet) beyond this legally required extent is not permitted without express written consent. KLÜBER LUBRICATION provides its customers with amended safety datasheets as prescribed by law. The customer is

Klübertemp GR RT 15

Version 1.4

Revision Date 07.07.2017

Print Date 07.07.2017

responsible for passing on safety datasheets and any amendments contained therein to its own customers, employees and other users of the product. KLÜBER LUBRICATION provides no guarantee that safety datasheets received by users from third parties are up-to-date. All information and instructions in this safety datasheets were compiled to the best of our knowledge and are based on the information available to us. The data provided are intended to describe the product in relation to the required safety measures; they are neither an assurance of characteristics nor a guarantee of the product's suitability for particular applications and do not justify any contractual legal relationships.