



# TORA

*Clear Hardium+ lens*



### FRAME

- Wraparound polycarbonate frame
- Integrated side and orbital protection
- Contoured temple set for improved fit
- Heat resistance : up to 90° C
- Extremely lightweight : 22 g.

### LENS

- Clear Polycarbonate 9D base curve for excellent field of vision and lateral coverage
- Optical quality class 1 (no distortion)
- Resistance to impact at extreme temperature
- 100% UV filtration (in conformity with EN170)
- Hardium+ technology = superior anti-scratch and anti-fog coating
- Visible Light Transmittance = 92%

### FIELDS OF USE

- Mechanical hazards (marking F - 45m/s)
  - solid particles projectiles (metal, wood...) riveting, grinding, stone cutting, drilling...
- Construction
- UV radiation (accidental electric arc)
- Mist

### DO NOT USE FOR

Does not protect against liquid, dust, molten metal, laser beam, or any kind of welding application.

### FRAME MARKING

*CE 166 FT*

CE = conformity marking  
 166 = n° of the standard  
 FT = impact resistance at extreme temperature (45m/s between -5° and +55°C)

### EUROPEAN STANDARD

This product conforms to the European Council Directive 89/686/EEC and with the EN166 : 2001

EC-Type Examination Certificate n° 1343

Issued by INSPEC (notified body n°0194)  
 Upper Wingbury Courtyard, Wingrave, Aylesbury  
 Buckinghamshire, HP22LW, England

*Conform to EN166 - EN170*

### LENS MARKING

*2C-1,2 . AOS . 1 . FT*

2C = UV filter with good color recognition (conform to EN170)  
 1,2 = shade number (clear lens)  
 AOS = manufacturer Aearo  
 1 = optical class (permanent wear)  
 FT = impact resistance at extreme temperature (45m/s between -5° and +55°C)

### PRODUCT REFERENCE

Product Code	Frame	Lens	Material
71501-00001CP			PC Hardium+

*Supplied with a nylon cord*