



## SAFETY DATA SHEET

### Platenclene 100ml Pump Spray

According to Regulation (EC) No 1907/2006, Annex II, as amended.

#### SECTION 1: Identification of the substance/mixture and of the company/undertaking

##### 1.1. Product identifier

Product name Platenclene 100ml Pump Spray

Product number APCL100, ZA

##### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Cleaning agent.

Uses advised against No specific uses advised against are identified.

##### 1.3. Details of the supplier of the safety data sheet

###### Supplier

AF INTERNATIONAL. A division of HK WENTWORTH LTD  
ASHBY PARK  
COALFIELD WAY  
ASHBY de la ZOUCH  
LEICESTERSHIRE. LE65 1JR  
UNITED KINGDOM  
+44 (0) 1530 419600  
+44 (0) 1530 416640  
info@hkw.co.uk

##### 1.4. Emergency telephone number

Emergency telephone +44 1865 407333

#### SECTION 2: Hazards identification

##### 2.1. Classification of the substance or mixture

###### Classification (EC 1272/2008)

Physical hazards Not Classified

Health hazards Asp. Tox. 1 - H304

Environmental hazards Not Classified

##### 2.2. Label elements

###### Pictogram



Signal word Danger

Hazard statements H304 May be fatal if swallowed and enters airways.

## Platencle 100ml Pump Spray

**Precautionary statements** P102 Keep out of reach of children.  
 P301+P310 IF SWALLOWED: Immediately call a POISON CENTER/ doctor.  
 P331 Do NOT induce vomiting.  
 P501 Dispose of contents/ container in accordance with national regulations.

**Contains** Hydrocarbons, C11-C14, isoalkanes, cyclics, <2% aromatics

### 2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

## SECTION 3: Composition/information on ingredients

### 3.2. Mixtures

<b>Hydrocarbons, C11-C14, isoalkanes, cyclics, &lt;2% aromatics</b>	<b>30-60%</b>
CAS number: —	EC number: 927-285-2
<b>Classification</b>	
Asp. Tox. 1 - H304	

The full text for all hazard statements is displayed in Section 16.

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

**General information** Get medical attention immediately. Show this Safety Data Sheet to the medical personnel.

**Inhalation** Remove affected person from source of contamination. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Maintain an open airway. Loosen tight clothing such as collar, tie or belt. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Place unconscious person on their side in the recovery position and ensure breathing can take place.

**Ingestion** Rinse mouth thoroughly with water. Remove any dentures. Give a few small glasses of water or milk to drink. Stop if the affected person feels sick as vomiting may be dangerous. Do not induce vomiting unless under the direction of medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Never give anything by mouth to an unconscious person. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Place unconscious person on their side in the recovery position and ensure breathing can take place. Maintain an open airway. Loosen tight clothing such as collar, tie or belt.

**Skin contact** Rinse with water.

**Eye contact** Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 10 minutes.

**Protection of first aiders** First aid personnel should wear appropriate protective equipment during any rescue. If it is suspected that volatile contaminants are still present around the affected person, first aid personnel should wear an appropriate respirator or self-contained breathing apparatus. Wash contaminated clothing thoroughly with water before removing it from the affected person, or wear gloves. It may be dangerous for first aid personnel to carry out mouth-to-mouth resuscitation.

### 4.2. Most important symptoms and effects, both acute and delayed

**General information** See Section 11 for additional information on health hazards. The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

**Inhalation** Prolonged inhalation of high concentrations may damage respiratory system.

## Platencle 100ml Pump Spray

<b>Ingestion</b>	Gastrointestinal symptoms, including upset stomach. Fumes from the stomach contents may be inhaled, resulting in the same symptoms as inhalation. Aspiration hazard if swallowed. Entry into the lungs following ingestion or vomiting may cause chemical pneumonitis.
<b>Skin contact</b>	Prolonged contact may cause dryness of the skin.
<b>Eye contact</b>	May cause temporary eye irritation.

### **4.3. Indication of any immediate medical attention and special treatment needed**

<b>Notes for the doctor</b>	Treat symptomatically.
-----------------------------	------------------------

## **SECTION 5: Firefighting measures**

### **5.1. Extinguishing media**

**Suitable extinguishing media** The product is not flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.

**Unsuitable extinguishing media** Do not use water jet as an extinguisher, as this will spread the fire.

### **5.2. Special hazards arising from the substance or mixture**

**Specific hazards** Containers can burst violently or explode when heated, due to excessive pressure build-up.

**Hazardous combustion products** Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

### **5.3. Advice for firefighters**

**Protective actions during firefighting** Avoid breathing fire gases or vapours. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapours and protect men stopping the leak. Control run-off water by containing and keeping it out of sewers and watercourses. If risk of water pollution occurs, notify appropriate authorities.

**Special protective equipment for firefighters** Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Firefighter's clothing conforming to European standard EN469 (including helmets, protective boots and gloves) will provide a basic level of protection for chemical incidents.

## **SECTION 6: Accidental release measures**

### **6.1. Personal precautions, protective equipment and emergency procedures**

**Personal precautions** No action shall be taken without appropriate training or involving any personal risk. Keep unnecessary and unprotected personnel away from the spillage. Wear protective clothing as described in Section 8 of this safety data sheet. Follow precautions for safe handling described in this safety data sheet. Wash thoroughly after dealing with a spillage. Ensure procedures and training for emergency decontamination and disposal are in place. Do not touch or walk into spilled material.

### **6.2. Environmental precautions**

**Environmental precautions** Avoid discharge into drains or watercourses or onto the ground.

### **6.3. Methods and material for containment and cleaning up**

## Platenclene 100ml Pump Spray

### Methods for cleaning up

Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Small Spillages: Collect spillage. Large Spillages: Absorb spillage with non-combustible, absorbent material. The contaminated absorbent may pose the same hazard as the spilled material. Collect and place in suitable waste disposal containers and seal securely. Label the containers containing waste and contaminated materials and remove from the area as soon as possible. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. For waste disposal, see Section 13.

### 6.4. Reference to other sections

**Reference to other sections** For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

#### Usage precautions

Keep out of the reach of children. Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimise spills. Keep container tightly sealed when not in use. Avoid the formation of mists. Do not handle until all safety precautions have been read and understood. Do not handle broken packages without protective equipment. Do not reuse empty containers.

#### Advice on general occupational hygiene

Wash promptly if skin becomes contaminated. Take off contaminated clothing. Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Wash at the end of each work shift and before eating, smoking and using the toilet. Change work clothing daily before leaving workplace.

### 7.2. Conditions for safe storage, including any incompatibilities

#### Storage precautions

Store locked up. Keep only in the original container. Keep container tightly closed, in a cool, well ventilated place. Keep containers upright. Protect containers from damage. Bund storage facilities to prevent soil and water pollution in the event of spillage. The storage area floor should be leak-tight, jointless and not absorbent.

#### Storage class

Chemical storage.

### 7.3. Specific end use(s)

#### Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

## SECTION 8: Exposure Controls/personal protection

### 8.1. Control parameters

### 8.2. Exposure controls

#### Protective equipment



#### Appropriate engineering controls

Provide adequate ventilation. Personal, workplace environment or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Use process enclosures, local exhaust ventilation or other engineering controls as the primary means to minimise worker exposure. Personal protective equipment should only be used if worker exposure cannot be controlled adequately by the engineering control measures. Ensure control measures are regularly inspected and maintained. Ensure operatives are trained to minimise exposure.

## Platencle 100ml Pump Spray

<b>Eye/face protection</b>	Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Personal protective equipment for eye and face protection should comply with European Standard EN166. Unless the assessment indicates a higher degree of protection is required, the following protection should be worn: Tight-fitting safety glasses.
<b>Hand protection</b>	Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. The most suitable glove should be chosen in consultation with the glove supplier/manufacturer, who can provide information about the breakthrough time of the glove material. To protect hands from chemicals, gloves should comply with European Standard EN374. Considering the data specified by the glove manufacturer, check during use that the gloves are retaining their protective properties and change them as soon as any deterioration is detected. Frequent changes are recommended.
<b>Other skin and body protection</b>	Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.
<b>Hygiene measures</b>	Provide eyewash station and safety shower. Contaminated work clothing should not be allowed out of the workplace. Wash contaminated clothing before reuse. Clean equipment and the work area every day. Good personal hygiene procedures should be implemented. Wash at the end of each work shift and before eating, smoking and using the toilet. When using do not eat, drink or smoke. Preventive industrial medical examinations should be carried out. Warn cleaning personnel of any hazardous properties of the product.
<b>Respiratory protection</b>	Respiratory protection complying with an approved standard should be worn if a risk assessment indicates inhalation of contaminants is possible. Ensure all respiratory protective equipment is suitable for its intended use and is 'CE'-marked. Check that the respirator fits tightly and the filter is changed regularly. Gas and combination filter cartridges should comply with European Standard EN14387. Full face mask respirators with replaceable filter cartridges should comply with European Standard EN136. Half mask and quarter mask respirators with replaceable filter cartridges should comply with European Standard EN140.
<b>Environmental exposure controls</b>	Keep container tightly sealed when not in use.

### SECTION 9: Physical and Chemical Properties

#### 9.1. Information on basic physical and chemical properties

<b>Appearance</b>	Liquid.
<b>Colour</b>	Colourless.
<b>Odour</b>	Characteristic.
<b>Odour threshold</b>	Not available.
<b>pH</b>	pH (concentrated solution): 5-7
<b>Melting point</b>	Not available.
<b>Initial boiling point and range</b>	Not available.
<b>Flash point</b>	> 60°C CC (Closed cup).
<b>Evaporation rate</b>	Not available.
<b>Evaporation factor</b>	Not available.
<b>Flammability (solid, gas)</b>	Not available.
<b>Upper/lower flammability or explosive limits</b>	Not available.
<b>Other flammability</b>	Not available.

## Platencle 100ml Pump Spray

Vapour pressure	Not available.
Vapour density	Not available.
Relative density	Not available.
Bulk density	Not available.
Solubility(ies)	Not available.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	1.48 mPa s @ 25°C
Explosive properties	Not considered to be explosive.
Oxidising properties	Does not meet the criteria for classification as oxidising.

### 9.2. Other information

#### SECTION 10: Stability and reactivity

##### 10.1. Reactivity

**Reactivity** There are no known reactivity hazards associated with this product.

##### 10.2. Chemical stability

**Stability** Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.

##### 10.3. Possibility of hazardous reactions

**Possibility of hazardous reactions** No potentially hazardous reactions known.

##### 10.4. Conditions to avoid

**Conditions to avoid** There are no known conditions that are likely to result in a hazardous situation.

##### 10.5. Incompatible materials

**Materials to avoid** No specific material or group of materials is likely to react with the product to produce a hazardous situation.

##### 10.6. Hazardous decomposition products

**Hazardous decomposition products** Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

#### SECTION 11: Toxicological information

##### 11.1. Information on toxicological effects

###### Acute toxicity - oral

**Notes (oral LD<sub>50</sub>)** Based on available data the classification criteria are not met.

###### Acute toxicity - dermal

**Notes (dermal LD<sub>50</sub>)** Based on available data the classification criteria are not met.

###### Acute toxicity - inhalation

**Notes (inhalation LC<sub>50</sub>)** Based on available data the classification criteria are not met.

###### Skin corrosion/irritation

## Platencle 100ml Pump Spray

<b>Animal data</b>	Based on available data the classification criteria are not met.
<b><u>Serious eye damage/irritation</u></b>	
<b>Serious eye damage/irritation</b>	Based on available data the classification criteria are not met.
<b><u>Respiratory sensitisation</u></b>	
<b>Respiratory sensitisation</b>	Based on available data the classification criteria are not met.
<b><u>Skin sensitisation</u></b>	
<b>Skin sensitisation</b>	Based on available data the classification criteria are not met.
<b><u>Germ cell mutagenicity</u></b>	
<b>Genotoxicity - in vitro</b>	Based on available data the classification criteria are not met.
<b><u>Carcinogenicity</u></b>	
<b>Carcinogenicity</b>	Based on available data the classification criteria are not met.
<b>IARC carcinogenicity</b>	None of the ingredients are listed or exempt.
<b><u>Reproductive toxicity</u></b>	
<b>Reproductive toxicity - fertility</b>	Based on available data the classification criteria are not met.
<b>Reproductive toxicity - development</b>	Based on available data the classification criteria are not met.
<b><u>Specific target organ toxicity - single exposure</u></b>	
<b>STOT - single exposure</b>	Not classified as a specific target organ toxicant after a single exposure.
<b><u>Specific target organ toxicity - repeated exposure</u></b>	
<b>STOT - repeated exposure</b>	Not classified as a specific target organ toxicant after repeated exposure.
<b><u>Aspiration hazard</u></b>	
<b>Aspiration hazard</b>	Asp. Tox. 1 - H304 May be fatal if swallowed and enters airways. Pneumonia may be the result if vomited material containing solvents reaches the lungs.
<b><u>General information</u></b>	
<b>General information</b>	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
<b>Inhalation</b>	Prolonged inhalation of high concentrations may damage respiratory system.
<b>Ingestion</b>	Gastrointestinal symptoms, including upset stomach. Fumes from the stomach contents may be inhaled, resulting in the same symptoms as inhalation. Aspiration hazard if swallowed. Entry into the lungs following ingestion or vomiting may cause chemical pneumonitis.
<b>Skin contact</b>	Prolonged contact may cause dryness of the skin.
<b>Eye contact</b>	May cause temporary eye irritation.
<b>Route of entry</b>	Ingestion Inhalation Skin and/or eye contact
<b>Target organs</b>	No specific target organs known.

### SECTION 12: Ecological Information

**Ecotoxicity** Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.

#### 12.1. Toxicity

**Toxicity** Based on available data the classification criteria are not met.

## Platencle 100ml Pump Spray

### 12.2. Persistence and degradability

**Persistence and degradability** The degradability of the product is not known.

### 12.3. Bioaccumulative potential

**Bioaccumulative potential** No data available on bioaccumulation.

**Partition coefficient** Not available.

### 12.4. Mobility in soil

**Mobility** No data available.

### 12.5. Results of PBT and vPvB assessment

### 12.6. Other adverse effects

**Other adverse effects** None known.

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

**General information** The generation of waste should be minimised or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. Disposal of this product, process solutions, residues and by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any local authority requirements. When handling waste, the safety precautions applying to handling of the product should be considered. Care should be taken when handling emptied containers that have not been thoroughly cleaned or rinsed out. Empty containers or liners may retain some product residues and hence be potentially hazardous.

**Disposal methods** Dispose of surplus products and those that cannot be recycled via a licensed waste disposal contractor. Waste, residues, empty containers, discarded work clothes and contaminated cleaning materials should be collected in designated containers, labelled with their contents. Incineration or landfill should only be considered when recycling is not feasible.

## SECTION 14: Transport information

**General** The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

### 14.1. UN number

Not applicable.

### 14.2. UN proper shipping name

Not applicable.

### 14.3. Transport hazard class(es)

No transport warning sign required.

### 14.4. Packing group

Not applicable.

### 14.5. Environmental hazards

**Environmentally hazardous substance/marine pollutant**

No.

### 14.6. Special precautions for user

Not applicable.



## Platencle 100ml Pump Spray

### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

<b>National regulations</b>	Health and Safety at Work etc. Act 1974 (as amended). The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (SI 2009 No. 716). The Carriage of Dangerous Goods and Use of Transportable Pressure Equipment Regulations 2009 (SI 2009 No. 1348) (as amended) ["CDG 2009"]. EH40/2005 Workplace exposure limits.
<b>EU legislation</b>	Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended). Commission Regulation (EU) No 453/2010 of 20 May 2010. Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended). Dangerous Preparations Directive 1999/45/EC. Dangerous Substances Directive 67/548/EEC.

#### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

### SECTION 16: Other information

<b>Classification procedures according to Regulation (EC) 1272/2008</b>	Asp. Tox. 1 - H304: : Calculation method.
<b>Training advice</b>	Read and follow manufacturer's recommendations. Only trained personnel should use this material.
<b>Issued by</b>	Bethan Massey
<b>Revision date</b>	24/05/2016
<b>Revision</b>	1
<b>SDS number</b>	191
<b>Hazard statements in full</b>	H304 May be fatal if swallowed and enters airways.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.