



Isoprobe® II Safety Oscilloscope Probes



- Fully insulated, high frequency oscilloscope probes. Supplied with plug-in reference lead
- Highly flexible coaxial cable
 - Insulated safety BNC plugs
 - Ergonomically designed probes with finger guards and stainless steel tips
 - Up to 1000V CATII IEC1010 rating
- UL

Typ / Type	Isoprobe® II - 10:1 HS	
Teilungsverhältnis / Dividing ratio / Rapport	10:1	
Eingangskapazität / Input capacitance / Capacité d'entrée	16 pF	
Kompensationsbereich / Compensation range / Plage de compensation (werkseitige Einstellung / works setting / réglage en usine)	10 pF ... 35 pF (25 pF)	
Eingangswiderstand / Input impedance / Résistance d'entrée	10 MΩ	
Frequenzbereich / Frequency range / Plage de fréquences	0 ... 250 MHz	
Anstiegszeit / Rise time / Temps de montée	1,2 ns	
Leitungslänge / Lead length / Longueur du câble	120 cm	
Bemessungsspannung (frequenzabhängig) Rated voltage (frequency-dependent) Tension assignée (fonction de la fréquence)	1000 V, CAT II (600 V, CAT III)	