


PK7524

PK-010-RFG14-QSPKG/US/ W

Pressure sensors



1: sealing FPM / DIN 3869-14

Made in Germany



Product characteristics

Electronic pressure monitor
Connector
Process connection: G ¼ A / M5 I
2 switching outputs
Measuring range: 0...10 bar / 0...145 psi

Application

Application	Type of pressure: relative pressure Liquids and gases	
Pressure rating	25 bar	362 psi
Bursting pressure min.	300 bar	4350 psi
Medium temperature [°C]	-25...80	

Electrical data

Electrical design	DC PNP	
Operating voltage [V]	9.6...32 DC	
Current consumption [mA]	< 25	
Insulation resistance [MΩ]	> 100 (500 V DC)	
Protection class	III	
Reverse polarity protection	yes	

Outputs

Output	2 switching outputs	
Output function	2 x normally open	
Current rating [mA]	500	
Voltage drop [V]	< 2	
Short-circuit protection	pulsed	
Overload protection	yes	
Switching frequency [Hz]	100	

Measuring / setting range

Measuring range	0...10 bar	0...145 psi
Setting range		
Set point, SP	0.3...10 bar	4.5...145 psi
Hysteresis	0.2 bar	2.9 psi

Accuracy / deviations

Deviations (% of value of measuring range)

PK7524

PK-010-RFG14-QSPKG/US/ W

Pressure sensors

Switch point accuracy	< ± 2.5 *)
Characteristics deviation	< ± 1.5 (BFSL) / < ± 2.5 (LS) **)
Repeatability	< ± 0.5
Temperature drift (/ 10 K)	< ± 0.5
in the temperature range [°C]	0...80

Software / programming

Adjustment of the switch point	setting rings
--------------------------------	---------------

Environment

Ambient temperature [°C]	-25...80
Storage temperature [°C]	-40...100
Protection	IP 67

Tests / approvals

EMC	EN 61000-4-2 ESD: 4 kV CD / 8 kV AD EN 61000-4-3 HF radiated: 10 V/m EN 61000-4-4 Burst: 2 kV EN 61000-4-6 HF conducted: 10 V
Shock resistance	DIN IEC 68-2-27: 50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6: 20 g (10...2000 Hz)
MTTF [Years]	513

Mechanical data

Process connection	G ¼ A / M5 I
Materials (wetted parts)	stainless steel 316L / 1.4404; FPM (Viton)
Housing materials	PBT (Pocan); PC (Makrolon); FPM (Viton); stainless steel 316L / 1.4404
Switching cycles min.	50 million
Tightening torque [Nm]	25
Weight [kg]	0.093


Displays / operating elements

Display	Switching status 2 x LED yellow
---------	---------------------------------

Electrical connection

Connection	M12 connector
------------	---------------

Wiring



Remarks

Remarks	*) Setting accuracy **) BFSL = Best Fit Straight Line / LS = Limit Value Setting
---------	---

Pack quantity [piece]	1
-----------------------	---