

xufn01321

plastic fibre optic for sensor - diffuse - positioning - standard - 2m - Sn18mm



Main

Range of product	OsiSense XU
Sensor name	XUF
[Sn] nominal sensing distance	0.018 m
End fitting type	M2.6 x 0.45, standard thread end fitting
Additional information	Trimable with XUFZ11 included

Complementary

Electronic sensor type	Photo-electric sensor
Sensor design	Fiber design
Product destination	XUDA
Optic fiber material	PMMA
Sheath material	PE
Detection system	Diffuse
Optic fiber use	Positioning
Optic fiber length	2 m
External diameter	1 mm
Minimum bending radius	10 mm
Head mounting	M4 x 0.7
Optic fiber core	2 x Ø 0.5 mm
Product weight	0.045 kg

Environment

Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...80 °C
Vibration resistance	7 gn at 10...55 Hz conforming to IEC 60068-2-27
Shock resistance	30 gn (duration = 11 ms) conforming to IEC 60068-2-27
IP degree of protection	IP64 conforming to IEC 60529 IP641 conforming to NF C 20-010

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0648 - Schneider Electric declaration of conformity

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.