

## Crimping pliers - CRIMPFOX 6T - 1212037

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




Crimping pliers, for ferrules according to DIN 46228 Parts 1+4, 0.25 - 6 mm<sup>2</sup>, lateral entry, trapezoidal crimping

### Product Features

- ✓ Comprehensive range of crimping pliers
- ✓ All ferrules can be optimally crimped with a minimum amount of effort even in the case of large conductor cross sections
- ✓ Marked die stations for precise processing of corresponding cross sections
- ✓ Consistently high crimping quality
- ✓ Unlockable pressure lock



### Key commercial data

Packing unit	1 PCE
GTIN	 4 046356 454049
Custom tariff number	82032000
Country of origin	SWEDEN

### Technical data

#### Dimensions

Length (b)	220 mm
Height	72 mm
Width (a)	22.5 mm

#### General

Color	black
-------	-------

## Crimping pliers - CRIMPFOX 6T - 1212037

### Technical data

#### General

Die station	Crimping position 1
Min. cross section	0.25 mm <sup>2</sup>
Max. cross section	6 mm <sup>2</sup>
AWG min	24
AWG max	10
Die station	Crimping position 2
Die station	Crimping position 3
Die station	Crimping position 4
Die station	Crimping position 5
Compression	Trapezoidal crimp
Type of contact	Ferrules

### Classifications

#### ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

#### UNSPSC

UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518

#### eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811

### Approvals

#### Approvals

## Crimping pliers - CRIMPFOX 6T - 1212037

### Approvals

Approvals

GOST

---

Ex Approvals

---

Approvals submitted

---

### Approval details



### Accessories

Accessories

Tools

Replacement spring - CRIMPFOX/ SPR-1 - 1212069



Spare recuperating spring

### Drawings

Product drawing

