


MATERIALS AND FINISHES

2.92 PLUG:  
SEE SD-73252-011

CABLE:  
TEMP-FLEX AIR CORE 086-2201

LABEL:  
BRADY PERMASLEEVE



89762-1325	120.0	3048	16.0
89762-1324	18.00	457.2	2.40
89762-1323	15.00	381.0	2.00
89762-1322	12.00	304.8	1.60
89762-1321	9.00	228.6	1.20
89762-1320	6.00	152.4	0.80
PART NO.	IN	MM	INSERTION LOSS MAX TO 40 GHz (dB)
	A		

VSWR 1.40 MAX TO 40 GHz

MIL-STD-348A, FIG. 323.1		INTERFACE	
SPECIFICATION		DESCRIPTION	
DIMENSION STYLE MM/IN		SCALE INCH	DESIGN UNITS INCH
DRAWN BY AROBERTSON		DATE 2013/03/20	TITLE 2.92 PLUG ST X2 ON TEMP-FLEX 086-2201 CABLE CA-292/292, EWR-4902
CHECKED BY SSS		DATE 2013/03/20	<b>molex</b>
APPROVED BY JWIENER		DATE 2013/03/27	
MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-89762-132	SHEET NO. 1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

CHG: ADD MOLEX TO LABEL

EC NO: URF2014-0398  
DRWN:JWIENER 2014/01/03  
CHKD:AZR 2014/01/03  
APPR:JWIENER 2014/01/09

REV	DESCRIPTION
A1	

QUALITY SYMBOLS	
$\nabla = 0$	
$\nabla = 0$	
$\nabla = 0$	
GENERAL TOLERANCES (UNLESS SPECIFIED)	
	mm
	INCH
4 PLACES	$\pm$ ---
3 PLACES	$\pm$ ---
2 PLACES	$\pm$ ---
1 PLACE	$\pm$ ---
0 PLACE	$\pm$ ---
ANGULAR $\pm 2^\circ$	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	