

Bottle Shapes, VG style

- Helashrink 150 Series, with rib



150 Series supplied.



150 Series boot recovered onto a connector.

Combinations "On request"					
Adhesive	Material				
	B7	G	J	H	L
WM250	√	√	√	√	-
W8	√	√	√	√	-
W24	√	√	√	√	√
W21	√	√	√	√	-
V9500	√	√	√	√	-
HMT200A	√	√	√	√	-
Without Adhesive	√	√	√	√	√

Standard combinations	
Article-No.	Type
401-52880	152-42-G
401-53880	153-42-G
401-54880	154-42-G
401-55880	155-42-G
401-56880	156-42-G
401-57980	157-43-G
401-58980	158-43-G
401-59980	159-43-G
401-60980	160-43-G
401-52780	152-41-G
401-53780	153-41-G
401-54780	154-41-G
401-55780	155-41-G
401-56780	156-41-G
401-59780	159-41-G
401-57880	157-42-G
401-58780	158-41-G
401-59780	159-41-G
401-59880	159-42-G
401-60780	160-41-G
401-60880	160-42-G

Bottle Shapes, VG style

• Helashrink 150 Series, with rib


This style is used in conjunction with a circular grooved adaptor, providing strain relief and environmental sealing. For VG shapes with portholes "P" please refer to product standards tables in the appendix.




150 Series supplied.



150 Series boot recovered onto a connector.



a: Expanded form (supplied)



b: Fully recovered form (after heating)

For Material / Adhesive selection and other information please refer to page 10.

Sizes and Type Table

Type	Designation as per VG-Norm	ØH min. a	ØH max. b	ØJ min. a	ØJ max. b	P ± 10%	R ± 10%	JO ± 10%	HW ± 20%	JW ± 20%	V ± 10%	T ± 20%
152-42	VG 95343 T06 B 001 A	24.0	10.5	24.0	6.0	38.0	21.0	10.0	1.6	0.5	3.0	1.0
153-42	VG 95343 T06 B 002 A	25.0	14.0	9.0	3.5	55.0	28.0	16.0	1.8	0.5	3.0	1.0
154-42	VG 95343 T06 B 003 A	30.0	14.0	30.0	6.0	55.0	32.0	13.0	1.8	1.0	3.0	1.0
155-42	VG 95343 T06 B 004 A	31.0	18.0	31.0	7.0	67.0	35.0	18.0	1.8	1.0	3.0	1.0
156-42	VG 95343 T06 B 005 A	36.0	22.5	36.0	8.5	80.0	42.0	20.0	2.0	1.0	3.0	1.0
157-43	VG 95343 T06 C 001 A	43.0	28.0	43.0	10.0	99.0	61.0	20.0	2.2	1.0	3.0	1.7
158-43	VG 95343 T06 C 002 A	60.0	35.0	60.0	16.0	130.0	72.0	38.0	3.2	1.5	3.0	1.7
159-43	VG 95343 T06 C 003 A	66.0	45.0	66.0	17.0	171.0	90.0	50.0	3.8	2.0	3.0	2.0
160-43	VG 95343 T06 C 004 A	82.0	58.0	82.0	27.0	213.0	113.0	62.0	3.8	3.8	3.0	2.0
152-41	VG 95343 T06 A 001 A	24.0	10.5	24.0	6.0	26.0	9.0	10.0	1.6	0.5	3.0	1.0
153-41	VG 95343 T06 A 002 A	25.0	14.0	9.0	3.5	40.0	13.0	16.0	1.8	0.5	3.0	1.0
154-41	VG 95343 T06 A 003 A	30.0	14.0	30.0	6.0	43.0	20.0	13.0	1.8	1.0	3.0	1.0
155-41	VG 95343 T06 A 004 A	31.0	18.0	31.0	7.0	47.0	15.0	18.0	1.8	1.0	3.0	1.0
156-41	VG 95343 T06 A 005 A	36.0	22.5	36.0	8.5	60.0	22.0	20.0	2.0	1.0	3.0	1.0
159-41	VG 95343 T06 A 008 A	66.0	45.0	66.0	17.0	130.0	50.0	50.0	3.8	2.0	3.0	2.0
157-42	VG 95343 T06 B 006 A	43.0	28.0	43.0	10.0	79.0	41.0	20.0	2.2	1.0	3.0	1.7
158-41	VG 95343 T06 A 007 A	60.0	35.0	60.0	16.0	90.0	32.0	38.0	3.2	1.5	3.0	1.7
159-41	VG 95343 T06 A 008 A	66.0	45.0	66.0	17.0	130.0	50.0	50.0	3.8	2.0	3.0	2.0
159-42	VG 95343 T06 B 008 A	66.0	45.0	66.0	17.0	150.0	70.0	50.0	3.8	2.0	3.0	2.0
160-41	VG 95343 T06 A 009 A	82.0	58.0	82.0	27.0	137.0	37.0	62.0	3.8	3.8	3.0	2.0
160-42	VG 95343 T06 B 009 A	82.0	58.0	82.0	27.0	158.0	58.0	62.0	3.8	3.8	3.0	2.0

All dimensions in mm. Subject to technical changes.