



Gewindeschneidsortimente Thread Cutting Assortments

EVENTUS
by EXACT

**STM
35**

M3 - M20



Technische Information

HSS = Hochleistungsschnell-Stahl
DIN 352 • Für metrisches ISO-Gewinde DIN 13, Toleranz 6H

Anwendung

Zum Schneiden von innen- und Aussengewinden.

Technical Information

HSS = High-speed-steel
DIN 352 • For metric ISO-thread DIN 13, tolerance 6H

Application

For cutting threads.

No.	M	M3 – M20	i	CODE
STM 35	metrisch / metric	Gewindeschneidsortiment, 52-teilig Thread Cutting Assortment, 52 pieces Handgewindebohrer (Vor-, Mittel-, Fertigschneider) Hand Taps (Taper, Second, Plug) M3 - M4 - M5 - M6 - M8 - M10 - M12 - M14 - M16 - M18 - M20 + Schneideisen Circular Dies M3 - M4 - M5 - M6 - M8 - M10 - M12 - M14 - M16 - M18 - M20 + Schneideisenhalter Holder for Circular Dies 20x5 / 20x7 / 25x9 / 30x11 / 38x14 / 45x18 + Windeisen Tap wrenches 1 + 3	HSS	10723