

JUMO GmbH & Co. KG
 Delivery address: Mackenrodtstraße 14
 36039 Fulda, Germany
 Postal address: 36035 Fulda, Germany
 Phone: +49 661 6003-0
 Fax: +49 661 6003-607
 E-mail: mail@jumo.net
 Internet: www.jumo.net

JUMO Instrument Co. Ltd.
 JUMO House
 Temple Bank, Riverway
 Harlow, Essex CM20 2DY, UK
 Phone: +44 1279 635533
 Fax: +44 1279 635262
 E-mail: sales@jumo.co.uk
 Internet: www.jumo.co.uk

JUMO Process Control, Inc.
 6733 Myers Road
 East Syracuse, NY 13057, USA
 Phone: 315-437-5866
 1-800-554-5866
 Fax: 315-437-5860
 E-mail: info.us@jumo.net
 Internet: www.jumousa.com



Lines, plugs and sockets for pH, redox, conductivity and temperature sensors

Brief description

The use of electrochemical sensors for liquid analysis requires special connection lines and connectors. JUMO offers a selection of tried and tested versions for this application. They are available either as a finished preassembled connection line, as loose material by the roll or as individual plugs/sockets for self-assembly.

As a general rule:


The measuring lead selected between an electrochemical sensor and the transmitter/indicator/controller should be as short as possible. Typical line lengths in this case are 5 to 10 m with high functional reliability. If longer line lengths must be selected in some cases, the technical documentation of the sensors and measuring instruments must be observed. The line between the sensor and evaluation instrument must be laid directly and without interruption (for example terminal strips) or cable extensions.

pH and redox measurement

Specially designed coaxial lines are used for pH and redox measurements. In these measurements direct voltages of a lower level are generated by the sensor and transferred to the evaluation instrument. These measurements, some of which are high-resistive measurements (potentiostatic measurement principle, internal resistors up to several gigaohms) are sensitive to electrical faults and radiation. Even a movement of the line can falsify measurement values in unfavorable conditions. An additional layer of insulation in JUMO coaxial line increases the insulation resistance of the line, thereby ensuring a reliable connection from the sensor to the transmitter. Other coaxial lines of the type used for antennas and computers are not suitable and could damage the sensors. This could also result in immediate failure of the sensor or reduced service life. For multiple sensors, for example with integrated temperature sensors, coax lines with individual core wires are available (Variopin, etc.).

Conductive conductivity measurement

Connecting cables for conductive conductivity probes as per data sheets 202922 to 202930 are also specially optimized and selected for the application. Alternating voltages of low amplitude in the range of a few Hertz to several Kilohertz are transferred. Accordingly these measuring leads are normally equipped with shielding. The shielding itself must be designed according to applicable technical rules and the relevant application. The individual core wires must be twisted for increased "twisted pair" signal reliability.



Type 202990/11-95-xx-xx-xx
with VP line socket

Key features

- High-quality preassembled connection lines
- Highest possible protection type with factory assembly
- Wide range of connectors/sockets and special selection
- Customer-specific versions on request

JUMO GmbH & Co. KG
 Delivery address: Mackenrodtstraße 14
 36039 Fulda, Germany
 Postal address: 36035 Fulda, Germany
 Phone: +49 661 6003-0
 Fax: +49 661 6003-607
 E-mail: mail@jumo.net
 Internet: www.jumo.net

JUMO Instrument Co. Ltd.
 JUMO House
 Temple Bank, Riverway
 Harlow, Essex CM20 2DY, UK
 Phone: +44 1279 635533
 Fax: +44 1279 635262
 E-mail: sales@jumo.co.uk
 Internet: www.jumo.co.uk

JUMO Process Control, Inc.
 6733 Myers Road
 East Syracuse, NY 13057, USA
 Phone: 315-437-5866
 1-800-554-5866
 Fax: 315-437-5860
 E-mail: info.us@jumo.net
 Internet: www.jumousa.com



Order details

(1) Basic type	
202990	Lines, plugs and sockets for pH, redox, conductivity and temperature sensors
(2) Type of line	
00	Without
02	Line for pH and redox, Ø 5 mm, 75 °C
09	Line for conductive conductivity probes, 4-core
11	VP coaxial line
(3) Connection end 1 (sensor side)	
00	Without
92	N line socket, rotating
95	VP line socket, 6-pin, for lines Ø 5 mm
(4) Line length	
for line type 02	
1,5	1.5 m
3	3 m
5	5 m
10	10 m
25	25 m
50	50 m
100	100 m
for line type 09	
25	25 m
50	50 m
for line type 11	
5	5 m
10	10 m
15	15 m
20	20 m
(5) Connection end 2 (device side)	
00	Without
04	N connector
11	Ferrules
13	Shield-Kon® connector
22	BNC connector, straight, for lines Ø 5 mm
23	BNC connector, angled, for lines Ø 5 mm
90	N line socket, for lines Ø 5 mm

Order code **(1)** / **(2)** - **(3)** - **(4)** - **(5)**
 Order example 202990 / 02 - 92 - 10 - 00

Minimum order quantity: Plugs and sockets, 5 pieces per type, deviating and preassembled line 10 pieces per type

JUMO GmbH & Co. KG
 Delivery address: Mackenrodtstraße 14
 36039 Fulda, Germany
 Postal address: 36035 Fulda, Germany
 Phone: +49 661 6003-0
 Fax: +49 661 6003-607
 E-mail: mail@jumo.net
 Internet: www.jumo.net

JUMO Instrument Co. Ltd.
 JUMO House
 Temple Bank, Riverway
 Harlow, Essex CM20 2DY, UK
 Phone: +44 1279 635533
 Fax: +44 1279 635262
 E-mail: sales@jumo.co.uk
 Internet: www.jumo.co.uk



JUMO Process Control, Inc.
 6733 Myers Road
 East Syracuse, NY 13057, USA
 Phone: 315-437-5866
 1-800-554-5866
 Fax: 315-437-5860
 E-mail: info.us@jumo.net
 Internet: www.jumousa.com






Stock versions (delivery 3 days after receipt of order)

Preassembled lines




Coaxial lines, Ø 5 mm for pH and redox electrodes, compensation thermometer and glass conductivity cells

Line end 1 (sensor side)	Type of line	Type	Old type	Line end 2 (device side)	Part no.
92 N-line socket, rotating	02 Low-noise coaxial line, temperature: -25 to +75, PVC, black			0 Without plug, without socket	
	Length 3 m:	202990/02-92-3-00	2992-2(3)-0		00082672
	Length 5 m:	202990/02-92-5-00	2992-2(5)-0		00082673
	Length 10 m:	202990/02-92-10-00	2992-2(10)-0		00082659
	Length 25 m:	202990/02-92-25-00	2992-2(25)-0		00082660
	Length 50 m:	202990/02-92-50-00	2992-2(50)-0		00303525
					

Coaxial lines, Ø 5 mm for pH and redox electrodes, compensation thermometer and glass conductivity cells

Line end 1 (sensor side)	Type of line	Type	Old type	Line end 2 (device side)	Part no.
92 N line socket, rotating	02 Low-noise coaxial line, temperature: -25 to +75, PVC, black			22 BNC connector, straight	
	Length 1 m:	202990/02-92-1-22	-		00328997
					

Coaxial lines, Ø 5 mm for pH and redox electrodes, compensation thermometer and glass conductivity cells

Line end 1 (sensor side)	Leitungsart	Type	Old type	Line end 2 (device side)	Part no.
92 N line socket, rotating	02 Low-noise coaxial line, temperature: -25 to +75, PVC, black			13 Shield-Kon® connector	
	Length 1,5 m:	202990/02-92-1,5-13	-		00085154
	Length 5 m:	202990/02-92-5-13	-		00307298
	Length 10 m:	202990/02-92-10-13	-		00082649
					

JUMO GmbH & Co. KG
 Delivery address: Mackenrodtstraße 14
 36039 Fulda, Germany
 Postal address: 36035 Fulda, Germany
 Phone: +49 661 6003-0
 Fax: +49 661 6003-607
 E-mail: mail@jumo.net
 Internet: www.jumo.net

JUMO Instrument Co. Ltd.
 JUMO House
 Temple Bank, Riverway
 Harlow, Essex CM20 2DY, UK
 Phone: +44 1279 635533
 Fax: +44 1279 635262
 E-mail: sales@jumo.co.uk
 Internet: www.jumo.co.uk

JUMO Process Control, Inc.
 6733 Myers Road
 East Syracuse, NY 13057, USA
 Phone: 315-437-5866
 1-800-554-5866
 Fax: 315-437-5860
 E-mail: info.us@jumo.net
 Internet: www.jumousa.com



Connecting cables for pH and redox electrodes and glass conductivity cells and multisensors with integrated temperature sensor; VP terminal head

Line end 1 (sensor side)	Type of line	Type	Old type	Line end 2 (device side)	Part no.
95 VP (Variopin)-line socket, 6-pin	11 VP (Variopin) coaxial line with shield +4 stranded wire and cable shield, temperature: -30 to +70, PVC, black Length 5 m: Length 10 m: Length 15 m:	202990/11-95-5-11 202990/11-95-10-11 202990/11-95-15-11	- - -	11 Ferrules	00372919 00373029 00451481

Diagram details: The cable has a diameter of $\phi 7.5$ mm. The length of the free end is 75 mm. The wiring is as follows: 1 (TR), 2 (RD), 3 (GY), 4 (BU), 5 (WH), 6 (GN), 7 (GN/YE). The contact assignment is: (1) pH glas, (2) pH reference, (3) Pt100/1000 (3-wire), (4) free, (5) Pt100/1000, (6) Pt100/1000, (7) Shield.

Contact assignment: (1) pH glas (2) pH reference (3) Pt100/1000 (3-wire) (4) free
 (5) Pt100/1000 (6) Pt100/1000 (7) Shield

Lines (by the roll without plugs or sockets)

Coaxial lines, ϕ 5 mm for pH and redox measurements

Line end 1 (sensor side)	Type of line	Type	Old type	Line end 2 (device side)	Part no.
0 Without plug, without socket	02 Low-noise coaxial line, temperature: -25 to +75, PVC, black Length 100 m:	202990/02-00-100-00	2990-2(100)-0	0 Without plug, without socket	00085976

Diagram details: The cable has a diameter of $\phi 5$ mm.

Connecting cables, ϕ 5.7 mm for conductive conductivity probes (2-electrode system)

Line end 1 (sensor side)	Type of line	Type	Old type	Line end 2 (device side)	Part no.
0 Without plug, without socket	09 4 stranded wire and shield temperature: -5 to +80 PVC, grey Length 25 m: Length 50 m:	202990/09-00-25-00 202990/09-00-50-00	2990-9(25)-0 2990-9(50)-0	0 Without plug, without socket	00303681 00304181

Diagram details: The cable has a diameter of $\phi 5.7$ mm. The length of the free end is 20 mm. The wiring is as follows: WH, BN, YE, GN.

Color coding to DIN IEC 757:

BU = Blue GN = Green GN/YE = Green/Yellow GY = Grey RD = Red TR = Transparent WH = White YE = Yellow




JUMO GmbH & Co. KG
 Delivery address: Mackenrodtstraße 14
 36039 Fulda, Germany
 Postal address: 36035 Fulda, Germany
 Phone: +49 661 6003-0
 Fax: +49 661 6003-607
 E-mail: mail@jumo.net
 Internet: www.jumo.net

JUMO Instrument Co. Ltd.
 JUMO House
 Temple Bank, Riverway
 Harlow, Essex CM20 2DY, UK
 Phone: +44 1279 635533
 Fax: +44 1279 635262
 E-mail: sales@jumo.co.uk
 Internet: www.jumo.co.uk


JUMO Process Control, Inc.
 6733 Myers Road
 East Syracuse, NY 13057, USA
 Phone: 315-437-5866
 1-800-554-5866
 Fax: 315-437-5860
 E-mail: info.us@jumo.net
 Internet: www.jumousa.com



Plugs¹ (for self-assembly on coaxial line)

Designation/illustration	Type	Old type	for line type	Part no.
N connector for line diameter Ø 5 mm: 	202990/00-00-000-04	2990-00-4	02	00061202
BNC connector, straight for line diameter Ø 5 mm: 	202990/00-00-000-22	2990-00-22	02	00068842
BNC connector, angled for line diameter Ø 5 mm: 	202990/00-00-000-23	2990-00-23	02	00064222

Sockets¹ (for self-assembly on coaxial line)

Designation/illustration	Type	Old type	for line type	Part no.
N line socket for line diameter Ø 5 mm: 	202990/00-00-000-90	2991-00-0	02	00057350

¹ **Minimum order quantity:** Plugs and sockets, 5 pieces per type, deviating and preassembled line 10 pieces per type