

XSDA400519H7

inductive sensor XSD 80x80x40 - plastic - Sn40mm - 24..240VAC - terminals



[Download your XSDA400519H7 datasheet](#)



[Characteristics](#) | [Documents & Downloads](#)

Main Hide

Range of product	OsiSense XS
Series name	General purpose
Sensor type	Inductive proximity sensor
Product specific application	-
Sensor name	XSD
Sensor design	Form 80 x 80 x 40
Size	40 mm
Body type	Fixed
Enclosure material	Plastic
Type of output signal	Discrete
Wiring technique	2-wire
[Sn] nominal sensing distance	40 mm
Discrete output function	1 NO or 1 NC programmable
Electrical connection	Screw-clamp terminals
[Us] rated supply voltage	24...240 V AC
IP degree of protection	IP67

Complementary Hide

Detection face	5 positions turret head
Detector flush mounting acceptance	Non flush mountable
Material	Plastic
Front material	Plastic
Output circuit type	AC
Cable entry	1 entry tapped for 1/2" NPT cable gland
Switching frequency	<= 10 Hz
Depth	40 mm
Height	100 mm
Width	80 mm

Environment Hide

Product certifications	CCC
Ambient air temperature for operation	-25...70 °C

Offer Sustainability Hide

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1136 - Schneider Electric declaration of

conformity

Reference not containing SVHC above the threshold

REACH
Product environmental profile
Product end of life instructions

Available  [download Product environmental](#)

Available  [download End of life manual](#)

Contractual warranty

Period

18 months

 **Hide**