

ML10/13.SF

ABB contact for United
Kingdom

General Information

Extended Product Type:	ML10/13.SF
Product ID:	1SNA199095R1300
EAN:	3472591990959
Catalog Description:	ML10/13.SF
Long Description:	ML10/13.SF Screw Clamp Terminal Blocks Fuse

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Screw Clamp Terminal Blocks

Ordering

EAN:	3472591990959
Minimum Order Quantity:	20 piece
Customs Tariff Number:	85361050

Dimensions

Product Net Width:	13 mm
Product Net Height:	85 mm
Product Net Depth:	58 mm
Product Net Weight:	0.051 kg

Container Information

Package Level 1 Units:	20 piece
Package Level 1 Width:	172 mm
Package Level 1 Height:	71 mm
Package Level 1 Length:	155 mm
Package Level 1 Gross Weight:	1.020 kg
Package Level 1 EAN:	3472591990959
Package Level 2 Units:	200 piece
Package Level 2 Width:	300 mm
Package Level 2 Height:	300 mm
Package Level 2 Length:	500 mm
Package Level 2 Gross Weight:	10.700 kg
Package Level 3 Units:	4800 piece
Product Packing Type:	Box

Environmental

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Technical UL/CSA

ABB's website uses cookies. By staying here you are agreeing to our use of cookies. [Learn more](#)

Connecting Capacity UL/CSA:	Screw Clamp / Rigid 22-10 AWG
Flammability According to UL94:	V0

Additional Information

Color:	Black
Connecting Capacity-Main Circuit:	Screw Clamp / Flexible 1x 0.5-10 mm ² Screw Clamp / Rigid 1x 0.5-16 mm ²
Connection Type:	Screw clamp
Function:	Fuse
Gauge Type:	A6
IIT Publishing Status:	Level 0 - Information enabled
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Pollution Degree:	3
Product Main Type:	ML10/13.SF
Product Name:	Terminal block
Rated Cross-Section:	10 mm ²
Rated Current (I_n):	Main Circuit 10 A
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Rated Voltage (U_r):	800 V
Recommended Screw Driver:	5.5 mm
RoHS Date:	20050818
Spacing:	13 mm
Sub-Function:	For 6.3x25 and 6.3x32 Fuses
Wire Stripping Length:	12.0 mm

Certificates and Declarations (Document Number)

CSA Certificate:	TBD - OK in Ag.Base
cUL Certificate:	1SND161000A0202
Declaration of Conformity - CE:	1SND225007C1006
GOST Certificate:	1SND161005A1103
RoHS Information:	1SND230023F0206

Classifications

ETIM 4.0:	EC000899 - Fuse terminal block
ETIM 5.0:	EC000899 - Fuse terminal block
Object Classification Code:	X



