


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [87713-1001](#)  
**Status:** **Active**  
**Overview:** Serial ATA Host Receptacles  
**Description:** 1.27mm Pitch Serial ATA Host Receptacle, Surface Mount, Vertical, Standard Height, with 3.70mm Plastic Locating Peg, 0.76µm Gold (Au) Selective Plating, 22 Circuits, Lead-Free

**Documents:**

<a href="#">3D Model</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Product Literature (PDF)</a>
<a href="#">Product Specification PS-87713-016 (PDF)</a>	



**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	PCB Receptacles
Series	87713
Application	Board-to-Board, Signal
Comments	3.70mm Plastic Locating Peg
Overview	<a href="#">Serial ATA Host Receptacles</a>
Product Literature Order No	SNG-029
Product Name	Serial ATA
UPC	822348699360

**Physical**

(p)ower-(s)ignal Configuration	15p - 7s
Circuits (Loaded)	22
Circuits (maximum)	22
Durability (mating cycles max)	500
Flammability	94V-0
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.467/g
Number of Rows	1
Orientation	Vertical
PCB Locator	Yes
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Surface Mount

**Electrical**

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V

**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

87713Series

**Mates With**

87679 , 87799 , 87703

### **Solder Process Data**

Duration at Max. Process Temperature (seconds)	10
Lead-free Process Capability	Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	260

### **Material Info**

#### **Reference - Drawing Numbers**

Electrical Model Document	EE-78178-001, EE-78286-001, EE-78328-001, EE-78328-002, EE-87703-003, EE-87713-001
Product Specification	PS-87713-016
S-Parameter Model	SP-87713-001
Sales Drawing	SD-87713-001

This document was generated on 03/04/2015

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**