


LNGU 16-M




Abmessungen Dimensions	l	d	s	d ₁		
1607	16,600	13,200	10,00	5,70		

Abmessungen [mm]. / Dimensions [mm].

Werkzeuge siehe Seite: / See tools on pages: 76

Geometrie Geometry	ISO	Materialien / Grade						Radius	Vorschub pro Zahn Feed per tooth		Schnitttiefe Cutting depth	
		M9315	M9325	8215	8230	8240	r _c	f _{min}	f _{max}	a _{p min}	a _{p max}	
	LNGU 160708SR-M	●	●	●	●	●		0,8	0,10	0,25	1,0	13,0

LNGX 12-M



Abmessungen Dimensions	l	d	s	d ₁		
1205	12,000	9,500	7,10	4,50		

Abmessungen [mm]. / Dimensions [mm].

Werkzeuge siehe Seite: / See tools on pages: 70, 72, 74

Geometrie Geometry	ISO	Materialien / Grade						Radius	Vorschub pro Zahn Feed per tooth		Schnitttiefe Cutting depth	
		M9315	M9325	M9340	8215	8230	8240	r _c	f _{min}	f _{max}	a _{p min}	a _{p max}
	LNGX 120508ER-M	●	●	●	●	●		0,8	0,05	0,15	1,0	9,0