


Product

KCC 0908S




KCC-0908S is a crimping tool for coaxial connectors, 3.25 mm, 4.52 mm, 1.69 mm/.128", .178", .067", HEX- Crimp.

- High strength, through hardened alloy steel construction
- Unique mechanism significantly reduces hand force requirement over competing crimping tools
- Versatile and easy to customize for right hand or left hand users.
- Non-slip pad holds tool in place when leveraging on a work surface
- Full cycle crimp mechanism to ensure consistent, reliable crimp
- Ratchet release mechanism to clear miscrimps and obstructions
- Precision eccentric adjustment for consistent performance and ability to calibrate
- Hole in handle allows attachment of safety strap
- Each tool has a unique serial number for traceability



Die profile



Crimp profile

TECHNICAL DATA
Length: 204 mm/8.03"
Width: 22 mm/0.87"
Height: 76 mm/2.99"
Weight: 500 gr/1.1 lb
Crimp dimensions mm/ mm²:
3,25 mm/4,52 mm/1,69 mm
Crimp dimensions inch/ AWG:
.128"/.178"/.067"
Connector: Coaxial connector
Description: For example SMA,
SMB, SMC on RG 174, RG 179.
Life span, cycles: 50,000
Cables: RG122/ U, RG143A/ U,
RG174A/ U, RG179B/ U, RG180B/
U, RG187A/ U, RG188A/ U,
RG212/ U, RG222/ U, RG279/ U,
RG303/ U, RG316/ U, RG6 Quad,
RG6A/ U, TWINAX