



Data sheet




I _{max}	[A]	3.9
V _{max}	[Vdc]	8.8
P _c max	[W]	18.7
ΔT _{max}	[°C]	74
A	[mm]	20
A _l	[mm]	20
B	[mm]	20
H	[mm]	3.6
L	[mm]	100
Wire	AWG	n/a

- (At hot side temperature Th = 25°C / 298K, under dry N₂)
- P_c max = Cooling power at ΔT = 0 and I = I_{max}
- ΔT_{max} = Temperature difference at I = I_{max} and P_c = 0
- Max hot side temperature Th = 90°C for best long term performance
- Max mounting pressure: 1.5MPa
- Wires: UL-style 1569, 105°C (Unstripped)




Data sheet - At hot side temperature 25°C



*Note - Waste heat = Heat out of hot side




Data sheet - At hot side temperature 50°C



*Note - Waste heat = Heat out of hot side



Data sheet - At hot side temperature 75°C



*Note - Waste heat = Heat out of hot side