


1 U, 2 slot, with rear I/O

Part no.: 20836-145



Features:

- System for horizontal board mounting with board formats
 - Front: 6 U, 160 mm deep
 - Rear I/O: 6 U, 80 mm deep
- VME64x backplane
 - 2 slots, 6 U, with P0 connector
- ATX power supply, 250 W
- Heat dissipation with pull-out hot-swap fan unit
- Fan monitoring and voltage display



Technical information:

Height	Height	Depth	No. of slots	Description
1 U	44.45 mm	277.5 mm	2	1 U, 2 slot, with rear I/O

Delivery comprises: completely assembled, wired and tested

Item	Qty	Description
1	1	Shielded 19" chassis, steel, black powder-coated (RAL 9005)
2	2	Front slot; IEEE guide rails, incl. ESD clips (ESD clips fitted to the right), for horizontal rear I/O boards (6 U, 160 mm deep)
3	2	Rear slot; IEEE guide rails, incl. ESD clips (ESD clips fitted to the right), for horizontal mounting of rear I/O boards (6 U, 80 mm deep)
4	1	VME64x backplane for 6 U boards, 2 slots, with P0 connector; technical data under www.schroff.biz/oneclick enter 23001-603
5	1	ATX power supply; 250 W; Wide range input 100-240 V _{AC} ; output 3.3 V/14 A, 5 V/23 A, 12 V/16 A, -12 V/0.5 A; with IEC connector; mains switch; fan
6	1	Hot-swap fan unit with 4 fans; incl. fan monitoring and voltage display
7	1	DC switch (with LED), switches off only the DC output of the power supply unit, power ON
8	1	Cable harness to connect all system components

Note:

- System in accordance with IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11), backplane conforms to VITA 1.1-1997
- Please order equipment cable separately
- Version with 19" PSU available on request
- -48 V DC version on request