

DURACELL®

Rechargeable

DC1400

Size: C 2200mAh (HR14)
Rechargeable NiMH Battery

NiMH





Technical Specifications



Classification:	Cylindrical Rechargeable
Chemical system	Nickel Metal Hydride (Ni-MH)
Designation:	IEC – HR14
Nominal Voltage:	1.2V
Operating Voltage:	1.0V-1.35V
Operating temp:	-10°C to 50°C
Storage Temp:	5°C – 30°C
Typical weight:	61g
Typical Volume:	26.9 cubic centimeters
Typical Impedance:	30 milliohm @ 1 khz
Rated Capacity:	2200 mAh
Safety Features:	Pressure released resettable vent

BENEFITS

Reliable performance in everyday devices
1 charge up to 6 hours in toys



DURACELL®

BATTERIES

Berkshire Corporate Park
Bethel, CT 06801 U.S.A.
Tel: Toll free 1.800.544.5454
Web: www.Duracell.com

Information and contents in this data sheet are for reference purposes only. They do not constitute any warranty and representation is subject to change without notice. For most current information and further details, please contact Duracell.

Document #: CH-A