



ENGLISH

Datasheet

Stock No: 398-436

# RS Pro Clear Heat Shrink Tubing, 4.8mm, 2:1, 1.2m Length



## Product Details

PVDF Tubing (Rated to +175°C)

2:1 Shrink ratio

Thin wall semi-rigid Polyvinylidene

Flame retardant

Chemical, solvent, and abrasion resistant

Provides mechanical protection to wires and joints

Supplied in 1.2m lengths

Operating temperature	-55°C to +175°C
Low shrink temperature	+170°C (starts to shrink at 130°C)
Dielectric	43kV/mm

### Approvals

NASA SP-R-0022A Standard requirements TML 1.0% CVCM 0.1% Pass, IEC 60684-3-228

### Standards

AMS-DTL-23053/8, UL224 150°C, 600V VW-1 E75077 CSA C22,2 No 198, 1 150°C, 600V OFT VG 95343 Teil 5 typ.F

### High Temperature



ENGLISH

## Specifications:

Sleeve Diameter	4.8mm
Shrunk Diameter	2.4mm
Colour	Clear
Sleeve Type	Heat Shrink
Shrink Ratio	2:1
Sleeve Length	1.2m
Material	Fluoropolymer
Minimum Operating Temperature	-55°C
Maximum Operating Temperature	+175°C
Flame Retardant	Yes
Dielectric Strength	30kV/mm