

Professionally approved products.

Datasheet

Crimp Tool for Coaxial connectors

RS Stock number: 683-1627



Specifications:

- Non slip main handle and low friction moving handle ensure a comfortable hand grip
- Provides two-hand grip in the final phase of crimping, increasing comfort and productivity
- Full cycle crimp mechanism to ensure consistent, reliable crimp
- Ratchet release mechanism to clear mis-crimps and obstructions
- Precision eccentric adjustment for consistent performance and ability to calibrate
- Each tool has a unique serial number for traceability
- Durable: life span exceeds 50,000 cycles
- High strength, through hardened alloy Swedish steel construction

Crimp nest:	5.41 mm/.213" 6.48 mm/.255" 1.69 mm/.067"
Wire size:	RG108A/U, RG142B/U, RG210/U, RG223/U, RG302/U, RG58C/U, RG59B/U, RG62A/U, RG62B/U, RG71B/U
Connector:	Coaxial connector
Description:	For example BNC, TNC on RG 58, RG 59, RG 62, RG 71, Thinnet.
Crimp profile:	Hexagon
Length:	198 mm/7.8"
Width:	18 mm/0.71"
Height:	59 mm/2.32"
Weight:	350 g/0.77 lb
Life span, cycles:	50,000