




Physical Properties & Chemical Resistance of Polymers



	LDPE	HDPE	PP	PMP (TPX)	PVC	PC	PS	ACRYLIC (AC)	PTFE	PFA
Acids-Dilute	Excellent	Excellent	Excellent	Excellent	Excellent	Excellent	Excellent	Good	Excellent	Excellent
Acids-concentrated	Excellent	Excellent	Excellent	Excellent	Excellent	Limited	Limited	Limited	Excellent	Excellent
Alcohols	Excellent	Excellent	Excellent	Excellent	Excellent	Good	Good	Good	Excellent	Excellent
Aldehydes	Good	Good	Excellent	Good	Limited	Limited	Limited	Good	Excellent	Excellent
Bases	Excellent	Excellent	Excellent	Excellent	Excellent	Limited	Limited	Limited	Excellent	Excellent
Esters	Good	Good	Good	Good	Limited	Limited	Limited	Good	Excellent	Excellent
Hydrocarbons-aliphatic	Limited	Limited	Limited	Limited	Limited	Limited	Limited	Limited	Excellent	Excellent
Hydrocarbons-aromatic	Limited	Limited	Limited	Limited	Limited	Limited	Limited	Limited	Excellent	Excellent
Hydrocarbons-halogenated	Limited	Limited	Limited	Limited	Limited	Limited	Limited	Limited	Excellent	Excellent
Ketones	Good	Good	Good	Good	Limited	Limited	Limited	Good	Excellent	Excellent
Oils, mineral	Limited	Limited	Excellent	Excellent	Excellent	Excellent	Excellent	Excellent	Excellent	Excellent
Oils, vegetable	Limited	Limited	Good	Good	Good	Good	Good	Good	Excellent	Excellent
Oxidising agents	Limited	Limited	Limited	Limited	Limited	Limited	Limited	Limited	Excellent	Excellent

	LDPE	HDPE	PP	PMP (TPX)	PVC	PC	PS	ACRYLIC (AC)	PTFE	PFA
Max Temp °C	80	120*	135	180	70	130	70	90	300	270
Min Temp °C	-50	-100	-20*	-180	-25	-135	-40	-60	-200	-260
Autoclavable	NO	NO	YES	YES	NO	YES	NO	NO	YES	YES
Gas sterilisation	YES	YES	YES	YES	YES	YES	YES	YES	YES	YES
Dry Heat sterilisation	NO	NO	NO	YES	NO	NO	NO	NO	YES	YES
Gamma irradiation sterilisation	YES	YES	NO	YES	NO	YES	NO	YES	YES	YES
Chemical Disinfectant sterilisation	YES	YES	YES	YES	YES	YES	YES	NO	NO	YES
Transparency	TL	TL	TL	C	C	C	C	C	O	TL
Flexibility	F	R	R	R	R	R	R	R	R	F
Gas Permeability N ₂	20	3	4.4	65	0.4	3	3	-	-	-
Gas Permeability CO ₂	280	45	92	-	10.2	85	75	-	-	-
Gas Permeability O ₂	60	10	28	270	1.2	20	15	-	-	-
Water Absorbtion %	<0.01	<0.01	<0.02	<0.01	0.06	0.35	0.05	0.3	0.3	<0.03
Resistivity Ohm CM ²	>10 ¹⁵	>10 ¹⁵	>10 ¹⁶	>10 ¹⁶	<10 ¹⁶	2x10 ¹⁶	>10 ¹⁶	>10 ¹⁴	>10 ¹⁸	10 ¹⁸
Specific gravity	0.92	0.95	0.90	0.83	1.34	1.20	1.05	1.18	2.2	2.16

*Please note that the polymer may become malleable at temperatures above 80°C if the product is under structural stress.

*Warning. Material may become brittle at low temperatures

Use and Care of Plastics

Chemicals can affect the strength, flexibility, appearance, dimensions and weight of plastics depending on


length of exposure ...

the temperature ...

... the concentration.


Certain chemicals, i.e. detergents, lubricants, oils, pure water and surface additives in the presence of tensile stress can lead to cracking. Prolonged exposure to strong oxidising agents can also lead to embrittlement and failure.

Never place plastic labware in direct contact with a flame or directly onto a hotplate surface.



Generally, you can clean most plastic labware with laboratory detergent and rinse with distilled water.

Avoid using scourers or abrasive cleaners that scratch the plastic.



Particular care should be taken to avoid the use of strong alkali cleaners with polycarbonate. In the case of stains, oils, greases or other agents which cannot be removed by conventional washing you can adopt the following measures with care:

- Soaking in chromic acid solution will loosen organic particles.
- Bleaches (such as sodium hypochlorite if used at 20°C - 25°C will also assist in the cleaning of organically stained plastic labware. Not suitable for use with polycarbonate.
- Methylene chloride and acetone will help remove oils, however prolonged exposure to such organic solvents can cause swelling of certain plastics. In general do not use solvents with polycarbonate, PVC, acrylic or polystyrene.

For more detailed information on cleaning procedures contact our technical dept.