



Cable and Fibre Type

Grade of the cable: LSZH

Fibre type (ISO/IEC 11801-2002)		Outer Sheath Colour
62.5/125	OM1	Orange
50/125	OM2	Orange
50/125	OM3	Purple
09/125	OS1	Yellow

Id No.	Description	Ea
1.	LC Duplex Connector	2
2.	LC Boots	4
3.	LC Heat Shrink (Yellow+White)	2+2
4.	Identification Label	1
5.	1.6mm Duplex Cable (L m)	1
6.	Black Tape	2

Connector: LC clips shall be mounted on to the connector to make it duplex.

Optical Performance (IEC 61300-3-4):

Multimode (@ 1300nm)

LC : Max. IL - 0.30dB Typical: 0.20dB

Singlemode: (@1310nm and/or 1550nm)

LC : Max. IL - 0.30dB Typical: 0.20dB Return Loss: >50dB

RoHS Compliant

Coiling Diameter: Coiling Diameter of the patchcord shall be greater than 200mm

Packing: Each product shall be individually bagged and identified with a unique number printed on an ID label affixed to the product. Also, each product will be supplied with a Test Certificate.



REV	DESCRIPTION	DATE	DRN	APD	REV	DESCRIPTION (REVISION RECORD)	DATE	DRN	APD
MATERIAL		SIZE	TITLE		DGN				
FINISH		TOLERANCES UNLESS OTHERWISE SPECIFIED:	LC-LC Duplex PATCHCORD		DRN				
SCALE		0 PLC ± TOL0	PART NO.		DWC/REF NO.		CHD		
ALL DIMENSIONS IN MM		1 PLC ± TOL1	REV 01		SHEET 1 OF 1		QA VER		
		2 PLC ± TOL2	SIGNATURE		DATE				
		3 PLC ± TOL3							
		4 PLC ± TOL4							
		ANGLES ± ANG							