



# 739-8420 Data Sheet

ENGLISH

Model number : 739-8420  
Type of tool : Air Operated Shear  
Power source : Compressed air  
Maximum permissible operating pressure : 90 psi ( 6.2 bar )  
Recommended operating pressure : 90 psi ( 6.2 bar )

### Features

Ergonomic handle for operator comfort  
Heavy duty cutting blades for long life and reliable cutting  
Handle exhaust  
Fast cutting action

### Specifications

Material: Aluminium  
Cutting Capacity: 18 gauge (1.2mm) steel  
Free Speed: 2,000RPM  
Weight: 2.2kgs / 5lbs  
Length: 8.14" / 210mm  
Min Hose Size: 3/8" / 10mm  
Air inlet thread: 1/4"  
Sound: 86.7dBA  
Vibration: 4.1 m/s<sup>2</sup>  
Ave Air Consumption: 4cfm / 113 l/min  
Recommended lubrications: 10 Weight SAE Oil

# 739-8420

## Air Operated Shear

## Technical Data



### Declaration of Conformity

We	RS Components Ltd,
declare under our sole responsibility that the	739-8420 – Air Operated Shear
conforms with the directive and the standards	2006/42/EEC EN 792-6 ISO 28927