

Datasheet

RS Pro True OFF Delay Single Time Delay Relay, Screw, 0.6 → 600 s, DPDT, 2 Contacts, DPCO, 24 → 240 V ac/dc
RS Stock No: **896-6844**



Product Details

RS Pro true OFF delay single time delay relay is a multi-voltage, multi-range timer that is compact in size and suitable for DIN Rail mounting. It comes with a terminal screw type and has a time range of 0.6 to 600 s. It has DPDT, DPCO switch and contact configuration with 2 contacts and supply voltage of 24 to 240 V ac/dc.

Features and Benefits

- Power Off delay
- 22.5 mm width
- DIN rail mounting
- DPCO output relay
- 0.6 to 600 s timing range
- LED indication for power and relay status
- Supply voltage of 24-240 V ac/dc
- IP20 (terminals), IP40 (enclosure) protection

**Specifications:**

Number of Timer Functions	Single
Power Supply	External
Switch Configuration	DPCO
Time Increment	Seconds
Depth	100.5 mm
Length	75 mm
Maximum Operating Temperature	+60°C
Minimum Operating Temperature	-15°C
Number of Contacts	2
Width	22.5 mm
Contact Configuration	2CO
Current Maximum	5 A
Current Minimum	0.1 A
Maximum Voltage	240 V ac/dc
Minimum Voltage	24 V ac/dc
Mode of Operation	True Off Delay
Mounting Type	DIN Rail
Supply Voltage	24 to 240 V ac/dc
Terminal Type	Screw
Time Range	0.6 to 600 s
IP Rating	IP20, IP40