

Datasheet

RS Pro 50 Ω Right Angle PCB Mount MMCX Connector, jack, Solder Termination, 0 to 6GHz, Coaxial

RS Stock No: **921-0231**



Product Details

RS Pro PCB mount MMCX connector jack is suitable for operating frequencies ranging from 0 - 6 GHz. It is designed for 50 Ω impedance applications. This right angle, coaxial connector jack includes gold plated brass body and beryllium copper contacts for superior connectivity. This device 45% smaller in size making it ideal for space critical applications where limited board height is a concern. It is suitable for applications such as telecommunications and GPS markets.

Features and Benefits

- 3.5 mm flange
- Nominal impedance 50 Ω
- Suitable for applications such as telecommunications and GPS markets

**Specifications:**

Body Orientation	Right Angle
Body Plating	Gold
Cable Type	Coaxial
Contact Material	Beryllium Copper
Contact Plating	Gold
Gender	Female
Impedance	50 Ω
Mating Type	Snap-On
Mounting Type	PCB Mount
Operating Frequency	0 to 6 GHz
Size	Micro Miniature
Termination Method	Solder
Dimensions	6.8 x 6.5 mm
Operating Temperature Range	-55 to +165°C
Voltage Rating	250 V