

1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-11 GHz
- 1.2 NOMINAL IMPEDANCE: 50 OHMS
- 1.3 WORKING VOLTAGE: 1000 VOLTS MAX.
- 1.4 PROOF VOLTAGE: 2500 VOLTS
- 1.5 VSWR: 1.3 MAX.@10 GHz

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3804
- 2.2 CENTER CONTACT: BRASS PER JIS-C3804
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

3.1 SEE BELOW TABLE FOR DETAILS.


4.0 MECHANICAL

4.1 INTERFACE IN ACCORDANCE WITH: MIL-STD-348A

5.0 ENVIRONMENTAL

5.1 OPERATING TEMPERATURE RANGE: -85° C TO +165° C

9	SHELL	BRASS	1	NICKEL 100μ" MIN.
8	CHASSIS II	BRASS	1	NICKEL 100μ" MIN.
7	O-RING	SILICONE	1	RED
6	BODY II	BRASS	1	NICKEL 100μ" MIN.
5	INSULATION II	TEFLON	1	NONE
4	INSULATION I	TEFLON	1	NONE
3	CENTER CONTACT	BRASS	1	GOLD 30μ" MIN.
2	CHASSIS I	BRASS	1	NICKEL 100μ" MIN.
1	BODY I	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH



APPROVED by _____ DATE: _____



DESCRIPTION		N RIGHT ANGLE PLUG-JACK	
製圖	DRAWN	TOLERANCE	品名
	<i>Gina</i>	.X ±0.2	64-05 T.G.N
檢圖	CHECK	.XX ±0.1	TITLE
	<i>Arc</i>	.XXX ±0.05	\ROHS COMPLIANT (50Ω)
認定	APPROVAL	ANGLE ±5°	單位
	<i>Jenny</i>		mm(in)
		比例	DATE
		SCALE	10.27.11'
		UNIT	版次
		3:1	A-0
		DWG.NO.	64-0006