

For more Information
please call

1-800-Belden1



General Description:

20 AWG stranded (7x28) one tinned copper conductor, one bare copper conductor, polyethylene insulation, polyethylene inner jacket, Duofoil® (100% coverage) plus a tinned copper braid shield (85% coverage), PVC outer jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
1	20	7x28	TC - Tinned Copper	0.9398
			BC - Bare Copper	

Total Number of Conductors: 2

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PE - Polyethylene	0.610

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom Wall (mm)	Nom. Dia. (mm)
PE - Polyethylene	0.889	5.994

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	85

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.787

Overall Cable

Overall Nominal Diameter: 8.382 mm

Pair

Pair Color Code Chart:

Number	Color
1	Natural (bare copper conductor)
2	Natural (tinned copper conductor)

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +75°C

Bulk Cable Weight: 93.757 Kg/Km

Max. Recommended Pulling Tension: 498.198 N

Min. Bend Radius/Minor Axis: 88.900 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CL2, CMG

CEC/C(UL) Specification: CMG

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes
Customer Part Number Reference Specification:	IBM P/N 7362211

Flame Test

UL Flame Test:	UL1685 FT4 Loading
CSA Flame Test:	FT4

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	89207

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
100

Nom. Inductance:

Inductance (µH/m)
0.508555

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
47.5745

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
75.463

Nominal Velocity of Propagation:

VP (%)
66

Nominal Delay:

Delay (ns/m)
5.05274

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
31.1695

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
5.70894

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1	0.9843
10	3.9372
50	9.1868
100	13.4521
200	20.9984
400	33.4662

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Operating Voltage - Non-UL:

Voltage
600 V RMS

Put Ups and Colors:

METRIC MEASUREMENT VERSION

9207 Twinax - Twinaxial Cable

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9207 010U500	500 FT	33.000 LB	BLACK		100 OHM TWINAX
9207 010100	100 FT	7.100 LB	BLACK		100 OHM TWINAX
9207 0101000	1,000 FT	68.000 LB	BLACK	C	100 OHM TWINAX
9207 0101640	1,640 FT	111.520 LB	BLACK	C	100 OHM TWINAX
9207 0103280	3,280 FT	219.760 LB	BLACK	C	100 OHM TWINAX
9207 010500	500 FT	34.500 LB	BLACK	C	100 OHM TWINAX
9207 0105000	5,000 FT	350.000 LB	BLACK	C	100 OHM TWINAX

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 04-04-2017

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).