

# Wiha bits for drive system C<sub>4</sub>

For screw connections in miniature applications.

These bits fit directly in the machines of the manufacturers: **Perret**



## 7000 Z Standard bit, slotted, style C 4.

Material: High grade chrome-vanadium steel, through hardened.  
 Drive: DIN 3126, ISO 1173, style C 4.  
 Application: For particularly small screws.

Order-No.	⌀	↔	⊖	🔧
04728	0.8	28	0.20	10
04727	1.2	28	0.25	10
04726	1.5	28	0.25	10
04725	1.8	28	0.30	10
04724	2.0	28	0.40	10
04723	2.5	28	0.40	10
04722	3.0	28	0.50	10
04721	3.5	28	0.60	10
04729	4.0	28	0.80	10



## 7003 Z Standard bit, hex, style C 4.

Material: High grade chrome-vanadium steel, through hardened.  
 Drive: DIN 3126, ISO 1173, style C 4.  
 Application: For particularly small screws.

Order-No.	⌀	↔	🔧
04737	0.7	28	10
04736	0.9	28	10
04735	1.3	28	10
04734	1.5	28	10
04733	2.0	28	10
04732	2.5	28	10
04731	3.0	28	10
04730	4.0	28	10



## 7001 Z Standard bit, Phillips, style C 4.

Material: High grade chrome-vanadium steel, through hardened.  
 Drive: DIN 3126, ISO 1173, style C 4.  
 Application: For particularly small screws.

Order-No.	⊕	↔	🔧
04720	PH000	28	10
04719	PH00	28	10
04718	PH0	28	10
04717	PH1	28	10



## 7110M Universal holder, magnetic, style E 6.3.

Suitable for: For bits according to DIN 3126, ISO 1173 style C 4.  
 Drive: DIN 3126, ISO 1173, style E 6.3.  
 Application: Suitable for 4 mm bits, e.g. Wiha 7000-7005 series.  
 Extra: With magnet.

Order-No.	⊙	⊙	↔	🔧
32505	C4	1/4	60	10



## 7005 Z Standard bit, TORX®, style C 4.

Material: High grade chrome-vanadium steel, through hardened.  
 Drive: DIN 3126, ISO 1173, style C 4.  
 Application: For particularly small screws.

Order-No.	⊛	↔	🔧
20842	T3	28	10
20843	T4	28	10
04716	T5	28	10
04715	T6	28	10
04714	T7	28	10
04713	T8	28	10
04712	T9	28	10
04711	T10	28	10