

USB 3.0 to DVI External Video Card Multi Monitor Adapter with 1-Port USB Hub – 1920x1200

Product ID: USB32DVIEH



The USB32DVIEH USB 3.0 to DVI Adapter turns an available USB 3.0 port into a DVI output port with high resolution 1920x1200 video support. The adapter features built-in USB 3.0 pass-through, which offers a connection port in place of the USB port used for connecting the DVI adapter – an ideal workaround for Ultrabook™ or laptop users where only a limited number of USB ports are available.

The USB to DVI adapter functions as an external graphics card, providing a convenient way to add multi-monitor capability to a USB 3.0-enabled desktop or laptop computer (optimal performance from USB 3.0, backward compatible with USB 2.0). The included DVI to VGA adapter also allows you to use this device with a VGA display.

Leveraging the high-bandwidth (5 Gbps) SuperSpeed USB 3.0 interface, the adapter delivers smooth, high-definition content to your DVI display / projector. The adapter can be used to mirror your primary desktop, showing the same image on each display, or to extend your desktop to double your workspace and increase your productivity.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Recommended System Requirements:

CPU: Quad Core 2.4GHz or Higher (i5 recommended)

RAM: 4GB or higher

Certifications, Reports and Compatibility



Applications

- The 1-Port USB hub allows the use of another USB device without losing USB connectivity on your Ultrabook or slim laptop
- Add a secondary DVI display and extend your desktop without taking apart your computer to install a new video card
- Add multi-monitor capability to a single computer, to create engaging multimedia presentations
- Run multiple applications on different screens - check your email on one display and search the web on the other
- View large or multiple spreadsheets across multiple displays
- Use the adapter to connect your PC to your DVI-equipped projector or display for viewing family pictures and movies
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Features

- Supports resolutions up to 1920x1200
- Built in 1-Port USB 3.0 Hub
- SuperSpeed USB 3.0 (5 Gbps) Interface, backward compatible with USB 2.0
- Quick, easy installation
- USB-powered - No external power adapter required
- Choose between Mirrored, Extended or Primary display configurations
- Driver software supports display rotation
- Supports the use of multiple USB32DVIEH adapters on a single system (up to 5)
- DVI to VGA adapter included

Hardware	Warranty	2 Years
	Audio	No
	Chipset ID	MCT Trigger T6-688SL
	Industry Standards	SuperSpeed USB 3.0, USB 2.0
	Memory	16MB DDR II
	Output Signal	DVI-I (DVI Digital/Analog)
	USB Pass-Through	Yes
Performance	General Specifications	This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a DisplayLink or Fresco family chipset.
	Maximum Analog Resolutions	1920x1200
	Maximum Digital Resolutions	1920x1200
	Supported Resolutions	Widescreen(16/32 bit): 1920x1200, 1920x1080, 1680x1050, 1600x900, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720 Standard(16/32 bit): 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - USB Type-A (9 pin) USB 3.0 Male
	Connector B	1 - DVI-I (29 pin) Female
		1 - USB Type-A (9 pin) USB 3.0 Female
Software	Microsoft WHQL Certified	Yes
	OS Compatibility	Windows® 10 (32/64) Windows 8 / 8.1 (32/64) Windows 7(32/64) Windows Vista (32/64) Windows XP (32/64)
Special Notes / Requirements	Note	Connect a maximum of five USB32DVIEH adapters on a single PC - See manual for system requirements
	System and Cable Requirements	CPU: i3 Dual core 2.8GHz RAM: 2GB or higher Full HD Video: CPU: Quad Core 2.4GHz or Higher (i5 recommended) RAM: 4GB or higher

Power	Power Source	USB-Powered
Environmental	Humidity	< 85% non-condensing
	Operating Temperature	0°C to 50°C (32°F to 122°F)
	Storage Temperature	-10°C to 75°C (14°F to 167°F)
Physical Characteristics	Cable Length	160 mm [6.3 in]
	Color	Black
	Enclosure Type	Plastic
	Product Height	17 mm [0.7 in]
	Product Length	85 mm [3.3 in]
	Product Weight	75 g [2.6 oz]
	Product Width	49 mm [1.9 in]
Packaging Information	Shipping (Package) Weight	233 g [8.2 oz]
What's in the Box	Included in Package	1 - USB 3.0 to DVI Adapter
		1 - DVI to VGA adapter
		1 - Software CD
		1 - Manual

Product appearance and specifications are subject to change without notice.