



## SAFETY DATA SHEET

### AF Hearing Protection Cleaning Wipes Flat Pack

According to Regulation (EC) No 1907/2006, Annex II, as amended.

#### SECTION 1: Identification of the substance/mixture and of the company/undertaking

##### 1.1. Product identifier

**Product name** AF Hearing Protection Cleaning Wipes Flat Pack

**Product number** AEPCW040, ZA

##### 1.2. Relevant identified uses of the substance or mixture and uses advised against

**Identified uses** Cleaning agent.

**Uses advised against** No specific uses advised against are identified.

##### 1.3. Details of the supplier of the safety data sheet

**Supplier** AF INTERNATIONAL. A division of HK WENTWORTH LTD  
 ASHBY PARK  
 COALFIELD WAY  
 ASHBY de la ZOUCH  
 LEICESTERSHIRE. LE65 1JR  
 UNITED KINGDOM  
 +44 (0) 1530 419600  
 +44 (0) 1530 416640  
 info@hkw.co.uk

##### 1.4. Emergency telephone number

**Emergency telephone** +44 1865 407333

#### SECTION 2: Hazards identification

##### 2.1. Classification of the substance or mixture

###### Classification (EC 1272/2008)

**Physical hazards** Not Classified

**Health hazards** Not Classified

**Environmental hazards** Not Classified

##### 2.2. Label elements

**Hazard statements** EUH208 Contains Reaction mass of: 5-chloro-2-methyl-4-isothiazolin-3-one [EC no. 247-500-7] and 2-methyl-2H -isothiazol-3-one [EC no. 220-239-6] (3:1). May produce an allergic reaction.

**Precautionary statements** P102 Keep out of reach of children.

**Detergent labelling** < 5% perfumes, Contains D-LIMONENE, BENZISOTHIAZOLINONE, METHYLISOTHIAZOLINONE, METHYLCHLOROISOTHIAZOLINONE AND METHYLISOTHIAZOLINONE

##### 2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

## AF Hearing Protection Cleaning Wipes Flat Pack

### SECTION 3: Composition/information on ingredients

#### 3.2. Mixtures

<b>Propan-2-ol</b>		<b>5-10%</b>
CAS number: 67-63-0	EC number: 200-661-7	REACH registration number: 01-2119457558-25-XXXX
<b>Classification</b>		
Flam. Liq. 2 - H225		
Eye Irrit. 2 - H319		
STOT SE 3 - H336		

The full text for all hazard statements is displayed in Section 16.

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

<b>General information</b>	If in doubt, get medical attention promptly. Show this Safety Data Sheet to the medical personnel.
<b>Inhalation</b>	No specific recommendations. If throat irritation or coughing persists, proceed as follows. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Loosen tight clothing such as collar, tie or belt. Get medical attention if any discomfort continues.
<b>Ingestion</b>	No specific recommendations. If throat irritation or coughing persists, proceed as follows. Rinse mouth. Get medical attention if any discomfort continues.
<b>Skin contact</b>	No specific recommendations. Rinse with water. Get medical attention if any discomfort continues.
<b>Eye contact</b>	Rinse with water. Get medical attention if any discomfort continues.
<b>Protection of first aiders</b>	Use protective equipment appropriate for surrounding materials.

#### 4.2. Most important symptoms and effects, both acute and delayed

<b>General information</b>	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
<b>Inhalation</b>	No specific symptoms known. Spray/mists may cause respiratory tract irritation.
<b>Ingestion</b>	No specific symptoms known. May cause discomfort if swallowed.
<b>Skin contact</b>	No specific symptoms known. May cause discomfort.
<b>Eye contact</b>	No specific symptoms known. May be slightly irritating to eyes.

#### 4.3. Indication of any immediate medical attention and special treatment needed

<b>Notes for the doctor</b>	Treat symptomatically.
<b>Specific treatments</b>	No special treatment required.

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

<b>Suitable extinguishing media</b>	The product is not flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.
<b>Unsuitable extinguishing media</b>	Do not use water jet as an extinguisher, as this will spread the fire.

## AF Hearing Protection Cleaning Wipes Flat Pack

### 5.2. Special hazards arising from the substance or mixture

<b>Specific hazards</b>	Containers can burst violently or explode when heated, due to excessive pressure build-up.
<b>Hazardous combustion products</b>	Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

### 5.3. Advice for firefighters

<b>Protective actions during firefighting</b>	Avoid breathing fire gases or vapours. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapours and protect men stopping the leak.
<b>Special protective equipment for firefighters</b>	Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Firefighter's clothing conforming to European standard EN469 (including helmets, protective boots and gloves) will provide a basic level of protection for chemical incidents.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

<b>Personal precautions</b>	No specific recommendations. For personal protection, see Section 8.
-----------------------------	--

### 6.2. Environmental precautions

<b>Environmental precautions</b>	Avoid discharge to the aquatic environment.
----------------------------------	---

### 6.3. Methods and material for containment and cleaning up

<b>Methods for cleaning up</b>	Reuse or recycle products wherever possible. Absorb spillage to prevent material damage. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. Dispose of contents/container in accordance with national regulations.
--------------------------------	--

### 6.4. Reference to other sections

<b>Reference to other sections</b>	For personal protection, see Section 8.
------------------------------------	---

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

<b>Usage precautions</b>	Keep out of the reach of children. Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimise spills. Keep container tightly sealed when not in use. Avoid the formation of mists. Avoid discharge to the aquatic environment.
--------------------------	--

<b>Advice on general occupational hygiene</b>	Wash promptly if skin becomes contaminated. Take off contaminated clothing. Wash contaminated clothing before reuse.
---	--

### 7.2. Conditions for safe storage, including any incompatibilities

<b>Storage precautions</b>	No specific recommendations.
----------------------------	------------------------------

<b>Storage class</b>	Unspecified storage.
----------------------	----------------------

### 7.3. Specific end use(s)

<b>Specific end use(s)</b>	The identified uses for this product are detailed in Section 1.2.
----------------------------	---

## SECTION 8: Exposure Controls/personal protection

### 8.1. Control parameters

#### Occupational exposure limits

Propan-2-ol

## AF Hearing Protection Cleaning Wipes Flat Pack

Long-term exposure limit (8-hour TWA): WEL 400 ppm 999 mg/m<sup>3</sup>

Short-term exposure limit (15-minute): WEL 500 ppm 1250 mg/m<sup>3</sup>

### 2,6-Di-tert-butyl-p-cresol

Long-term exposure limit (8-hour TWA): WEL 10 mg/m<sup>3</sup>

### Ethanol

Long-term exposure limit (8-hour TWA): WEL 1000 ppm 1920 mg/m<sup>3</sup>

WEL = Workplace Exposure Limit

## 8.2. Exposure controls

<b>Appropriate engineering controls</b>	No specific ventilation requirements.
<b>Eye/face protection</b>	No specific eye protection required during normal use.
<b>Hand protection</b>	No specific hand protection recommended.
<b>Hygiene measures</b>	Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product. Wash contaminated clothing before reuse.
<b>Respiratory protection</b>	No specific requirements are anticipated under normal conditions of use. No specific recommendations. Provide adequate ventilation.
<b>Environmental exposure controls</b>	Not regarded as dangerous for the environment.

## SECTION 9: Physical and Chemical Properties

### 9.1. Information on basic physical and chemical properties

<b>Appearance</b>	Liquid-impregnated wipe.
<b>Colour</b>	Colourless.
<b>Odour</b>	Characteristic.
<b>Odour threshold</b>	Not available.
<b>pH</b>	Not available.
<b>Melting point</b>	Not available.
<b>Initial boiling point and range</b>	Not available.
<b>Flash point</b>	Not available.
<b>Evaporation rate</b>	Not available.
<b>Evaporation factor</b>	Not available.
<b>Flammability (solid, gas)</b>	Not available.
<b>Upper/lower flammability or explosive limits</b>	Not available.
<b>Other flammability</b>	Not available.
<b>Vapour pressure</b>	Not available.
<b>Vapour density</b>	Not available.
<b>Relative density</b>	Not available.
<b>Bulk density</b>	Not available.
<b>Solubility(ies)</b>	Not available.

## AF Hearing Protection Cleaning Wipes Flat Pack

<b>Partition coefficient</b>	Not available.
<b>Auto-ignition temperature</b>	Not available.
<b>Decomposition Temperature</b>	Not available.
<b>Viscosity</b>	Not available.
<b>Explosive properties</b>	Not considered to be explosive.
<b>Oxidising properties</b>	Does not meet the criteria for classification as oxidising.

### 9.2. Other information

#### SECTION 10: Stability and reactivity

##### 10.1. Reactivity

**Reactivity** There are no known reactivity hazards associated with this product.

##### 10.2. Chemical stability

**Stability** Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.

##### 10.3. Possibility of hazardous reactions

**Possibility of hazardous reactions** No potentially hazardous reactions known.

##### 10.4. Conditions to avoid

**Conditions to avoid** There are no known conditions that are likely to result in a hazardous situation.

##### 10.5. Incompatible materials

**Materials to avoid** No specific material or group of materials is likely to react with the product to produce a hazardous situation.

##### 10.6. Hazardous decomposition products

**Hazardous decomposition products** Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

#### SECTION 11: Toxicological information

##### 11.1. Information on toxicological effects

**Toxicological effects** Not regarded as a health hazard under current legislation.

##### Acute toxicity - oral

**Notes (oral LD<sub>50</sub>)** Based on available data the classification criteria are not met.

##### Acute toxicity - dermal

**Notes (dermal LD<sub>50</sub>)** Based on available data the classification criteria are not met.

##### Acute toxicity - inhalation

**Notes (inhalation LC<sub>50</sub>)** Based on available data the classification criteria are not met.

##### Skin corrosion/irritation

**Animal data** Based on available data the classification criteria are not met.

##### Serious eye damage/irritation

**Serious eye damage/irritation** Based on available data the classification criteria are not met.

##### Respiratory sensitisation

## AF Hearing Protection Cleaning Wipes Flat Pack

<b>Respiratory sensitisation</b>	Based on available data the classification criteria are not met.
<b><u>Skin sensitisation</u></b>	
<b>Skin sensitisation</b>	Based on available data the classification criteria are not met.
<b><u>Germ cell mutagenicity</u></b>	
<b>Genotoxicity - in vitro</b>	Based on available data the classification criteria are not met.
<b><u>Carcinogenicity</u></b>	
<b>Carcinogenicity</b>	Based on available data the classification criteria are not met.
<b>IARC carcinogenicity</b>	Contains a substance/a group of substances which may cause cancer. IARC Group 1 Carcinogenic to humans.
<b><u>Reproductive toxicity</u></b>	
<b>Reproductive toxicity - fertility</b>	Based on available data the classification criteria are not met.
<b>Reproductive toxicity - development</b>	Based on available data the classification criteria are not met.
<b><u>Specific target organ toxicity - single exposure</u></b>	
<b>STOT - single exposure</b>	Not classified as a specific target organ toxicant after a single exposure.
<b><u>Specific target organ toxicity - repeated exposure</u></b>	
<b>STOT - repeated exposure</b>	Not classified as a specific target organ toxicant after repeated exposure.
<b><u>Aspiration hazard</u></b>	
<b>Aspiration hazard</b>	Based on available data the classification criteria are not met.
<b>General information</b>	No specific health hazards known. The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
<b>Inhalation</b>	No specific symptoms known. Spray/mists may cause respiratory tract irritation.
<b>Ingestion</b>	No specific symptoms known. May cause discomfort if swallowed.
<b>Skin contact</b>	No specific symptoms known. May cause discomfort.
<b>Eye contact</b>	No specific symptoms known. May be slightly irritating to eyes.
<b>Route of entry</b>	Ingestion Inhalation Skin and/or eye contact
<b>Target organs</b>	No specific target organs known.
<b><u>Toxicological information on ingredients.</u></b>	

### Propan-2-ol

#### Acute toxicity - dermal

**Notes (dermal LD<sub>50</sub>)** LD<sub>50</sub> 5840 mg/kg, Oral, Rat REACH dossier information. Based on available data the classification criteria are not met.

#### Skin corrosion/irritation

**Animal data** Primary dermal irritation index: 0 REACH dossier information. Based on available data the classification criteria are not met.

#### Serious eye damage/irritation

**Serious eye damage/irritation** Dose: 0.1 mL, 1 second, Rabbit Causes serious eye irritation.

## AF Hearing Protection Cleaning Wipes Flat Pack

### Skin sensitisation

**Skin sensitisation** Buehler test - Guinea pig: Not sensitising. REACH dossier information. Based on available data the classification criteria are not met.

### Germ cell mutagenicity

**Genotoxicity - in vitro** Gene mutation: Negative. REACH dossier information. Based on available data the classification criteria are not met.

**Genotoxicity - in vivo** Chromosome aberration: Negative. REACH dossier information. Based on available data the classification criteria are not met.

### Carcinogenicity

**Carcinogenicity** NOAEL 5000 ppm, Inhalation, Rat REACH dossier information. Based on available data the classification criteria are not met.

**IARC carcinogenicity** IARC Group 3 Not classifiable as to its carcinogenicity to humans.

### Specific target organ toxicity - single exposure

**STOT - single exposure** STOT SE 3 - H336 May cause drowsiness or dizziness.

**Target organs** Central nervous system

### Specific target organ toxicity - repeated exposure

**STOT - repeated exposure** NOAEC 5000 ppm, Inhalation, Rat REACH dossier information. Based on available data the classification criteria are not met.

## SECTION 12: Ecological Information

**Ecotoxicity** Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.

### 12.1. Toxicity

**Toxicity** Based on available data the classification criteria are not met.

### Ecological information on ingredients.

#### Propan-2-ol

**Toxicity** Aquatic toxicity is unlikely to occur. Based on available data the classification criteria are not met.

**Acute toxicity - fish** LC<sub>50</sub>, 96 hours: 10000 mg/l, Pimephales promelas (Fat-head Minnow)

**Acute toxicity - aquatic invertebrates** LC<sub>50</sub>, 24 hours: >10000 mg/l, Daphnia magna

**Acute toxicity - aquatic plants** EC<sub>50</sub>, 7 days: 1800 mg/l, Scenedesmus quadricauda

### 12.2. Persistence and degradability

**Persistence and degradability** The degradability of the product is not known.

### Ecological information on ingredients.

#### Propan-2-ol

**Persistence and degradability** The substance is readily biodegradable.

## AF Hearing Protection Cleaning Wipes Flat Pack

**Biodegradation** Water - Degradation 53%: 5 days

**Biological oxygen demand** 1.19-1.72 g O<sub>2</sub>/g substance

**Chemical oxygen demand** 2.23 g O<sub>2</sub>/g substance

### 12.3. Bioaccumulative potential

**Bioaccumulative potential** No data available on bioaccumulation.

**Partition coefficient** Not available.

### Ecological information on ingredients.

#### Propan-2-ol

**Bioaccumulative potential** Bioaccumulation is unlikely.

### 12.4. Mobility in soil

**Mobility** No data available.

### Ecological information on ingredients.

#### Propan-2-ol

**Mobility** The product is soluble in water.

### 12.5. Results of PBT and vPvB assessment

### Ecological information on ingredients.

#### Propan-2-ol

**Results of PBT and vPvB assessment** This substance is not classified as PBT or vPvB according to current EU criteria.

### 12.6. Other adverse effects

**Other adverse effects** None known.

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

**General information** The generation of waste should be minimised or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way.

**Disposal methods** Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

## SECTION 14: Transport information

**General** The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

### 14.1. UN number

Not applicable.

### 14.2. UN proper shipping name

Not applicable.

### 14.3. Transport hazard class(es)



## AF Hearing Protection Cleaning Wipes Flat Pack

No transport warning sign required.

### 14.4. Packing group

Not applicable.

### 14.5. Environmental hazards

**Environmentally hazardous substance/marine pollutant**

No.

### 14.6. Special precautions for user

Not applicable.

### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

**Annex II of MARPOL 73/78  
and the IBC Code**

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### **National regulations**

Health and Safety at Work etc. Act 1974 (as amended).

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (SI 2009 No. 716).

The Carriage of Dangerous Goods and Use of Transportable Pressure Equipment Regulations 2009 (SI 2009 No. 1348) (as amended) ["CDG 2009"].

EH40/2005 Workplace exposure limits.

#### **EU legislation**

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended).

Commission Regulation (EU) No 453/2010 of 20 May 2010.

Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).

Dangerous Preparations Directive 1999/45/EC.

Dangerous Substances Directive 67/548/EEC.

### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

## SECTION 16: Other information

#### **Training advice**

Read and follow manufacturer's recommendations.

#### **Issued by**

Bethan Massey

#### **Revision date**

28/07/2016

#### **Revision**

0

#### **SDS number**

391

## AF Hearing Protection Cleaning Wipes Flat Pack

### Hazard statements in full

H225 Highly flammable liquid and vapour.

H319 Causes serious eye irritation.

H336 May cause drowsiness or dizziness.

H400 Very toxic to aquatic life.

H410 Very toxic to aquatic life with long lasting effects.

EUH208 Contains Reaction mass of: 5-chloro-2-methyl-4-isothiazolin-3-one [EC no. 247-500-7] and 2-methyl-2H -isothiazol-3-one [EC no. 220-239-6] (3:1). May produce an allergic reaction.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.