

## SKINTOP® KR-M ATEX plus

SKINTOP® KR-M ATEX plus, metric plastic cable gland with high degree of protection and reducing seal insert, explosion proof



Variety of approval certifications



Reliability



Optimum strain relief



Mechanical resistance



Oil & Gas

### Benefits

For the benefits, refer to SKINTOP® K-M ATEX plus

### Application range

With reducing seal insert, to seal cables with smaller outer diameters.

### Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

**SKINTOP® KR-M ATEX plus****Technical Data**

Classification:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland
Caution:	Refer to the instruction leaflet for the installation dimensions and torques
Certifications:	CE 0637 Ex II 2G Ex eb IIC Ex II 1D Ex ta IIIC IECEX IBE 13.0027X
Colour delivered:	RAL 9005 black/UV-resistant
Material:	Body: special polyamide Seal: special elastomer O-ring: CR
Tests:	DIN EN 60079-0 DIN EN 60079-7 DIN EN 60079-31
Protection rating:	IP 68 - 10 bar
Temperature range:	-20°C to +80°C

**Note**

Photographs are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINTOP® KR-M ATEX plus**

Article number	Article designation / size	Clamping range ØF (mm)	Thread M	SW mm	Total length C (mm)	Thread length, D (mm)
SKINTOP® KR-M ATEX plus						
54115205	KR-M 12 ATEX plus	2 - 4	12 x 1.5	15	30	8
54115215	KR-M 16 ATEX plus	4 - 6	16 x 1.5	19	34	8
54115225	KR-M 20 ATEX plus	5 - 10	20 x 1.5	25	38	9
54115235	KR-M 25 ATEX plus	6 - 13	25 x 1.5	30	40	10
54115245	KR-M 32 ATEX plus	9 - 15	32 x 1.5	36	47	10
54115255	KR-M 40 ATEX plus	16 - 23	40 x 1.5	46	52	10
54115265	KR-M 50 ATEX plus	22 - 29	50 x 1.5	55	62	12
54115275	KR-M 63 ATEX plus	29 - 39	63 x 1.5	66	71	12

Last Update (04.07.2017)

©2017 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03.16