

# POLYETHYLENE (PE) TUBING

[✉ Email](#)[🖨 Print](#)

Parker Legris offers two types of polyethylene tubing: "Advanced PE" 50% reticulated and Low Density PE.

Our range of "Advanced PE" is designed for demanding environments, especially that of water treatment, without compromising operator safety.

**PART NUMBER:**

1015Y08F00

**TUBE I.D. (MM):**

5,75

**TUBE I.D. (INCH):**

na

**TUBE O.D. (MM):**

8

**TUBE O.D. (INCH):**

na

**COLOR:**

NATURAL

**LENGTH (M):**

150

**LENGTH (INCH):**

na

[Reset Attributes](#)

**WHERE TO BUY****PRODUCT OVERVIEW****TECH SPECIFICATIONS**

[Print Tech Specifications](#)

**PERFORMANCE CHARACTERISTICS****MAXIMUM PRESSURE (BARG)**

16

**MINIMUM WORKING TEMPERATURE (°C)**

-40

**MAXIMUM WORKING TEMPERATURE (C)**

95

**VACUUM RATING (MM OF HG)**

755

**WEIGHT (KG/PACKAGE)**

4.05

**MAXIMUM BEND RADIUS (MM)**

40

**MAXIMUM BEND RADIUS (INCH)**

na

**NUMBER OF TUBES**

1

**APPLICATION**

Beverage, Chemical, Petrochemical, Food Process, Water, Water Treatment

**MEDIA**

Advanced PE: Water, beverages and other fluids/Low Density  
PE: Industrial fluids

**CERTIFICATES**

Advanced PE Tubing: FDA: 21 CFR 177.1520, RG: 1935/2004/EC, DI: 97/23/EC (PED), DI: 2002/95/EC (RoHS), 2011/65/EC, NSF 42/58 (1/4" and 3/8" approved for 10 bar and 1/2" approved for 8 bar at room temperature), NSF 51, 61 C-HOT, ACS (except for purple co

[Print Tech Specifications](#)

## PRODUCT SUPPORT

### RECOMMENDED



Fittings and Tees



Polyamide (PA) Flexible Tubing



Fluoropolymer (PFA) Tubing



Polyurethane (PU) Tubing

### CONTACT US

#### Parker Hannifin Manufacturing France SAS

Fluid System Connectors Division Europe  
Parc Alcyone - Bat. D  
1 rue André et Yvonne Meynier - CS 46911  
35069 Rennes Cedex France

#### Phone

Phone: +33 (0) 2-99-25-55-00

 | [EMAIL PARKER](#)

### Parker Hannifin

[Products](#)

[Investors](#)

[Careers](#)

[About Parker](#)

[Community](#)