



Data Sheet



ENGLISH

5 Level Clock Irreversible Labels

A temperature test strip that will record permanently the highest bracketed temperature reached by the label.



Application:

Peel temperature indicating label from backing paper. Apply to dust and grease free surface. Indicators change from white/grey to black when the temperature rating has been achieved. Note that labels with a polyimide film will appear orange to start. These products are made to the highest standards however they are not suitable for all applications. **Please discuss any specific needs with our team.**

Physical Properties: (Not for specification purposes)

	Low Temperatures (171°C and below)	Mid Temperatures (177°C to 210°C)	High Temperatures (210°C+)
Adhesive Type	Acrylic	Modified Acrylic	Modified Acrylic
Carrier	Polyester	Tissue	Tissue
Covering Film	Polyester	Kaladex	Polyimide
Colour Change Material	Non-toxic, white crystalline solid on a black absorbent backing, adhered with acrylic adhesive		
Tolerance	29 to 99°C = ±1°C, 100 to 154°C = ±1.5°C and 160 to 280°C = ±1% +1°C		
Shelf Life	Temperatures from 29 – 34°C / 84 – 93°F = 6 months storage life, providing they are stored in a refrigerator inside a sealed bag. Temperatures from 37 – 49°C / 99 – 120°F = 12 months storage life, providing they are stored in a refrigerator inside a sealed bag. Temperatures from 54 – 290° / 130 – 554°F = 24 months storage life, store at room temperature & Humidity (i.e. 20°C/68°F & 50% relative humidity)		

RS Order Code	Description	Temperatures	Dimensions
285964	5 Level Clock Range 1	40-54°C	15mm diameter
285970	5 Level Clock Range 2	60-82°C	15mm diameter
285986	5 Level Clock Range 3	88-110°C	15mm diameter
285992	5 Level Clock Range 4	116-138°C	15mm diameter
286002	5 Level Clock Range 5	143-166°C	15mm diameter
286018	5 Level Clock Range 6	171-193°C	15mm diameter