



SAFETY DATA SHEET

SAPPHIRE AQUA 2

Page: 1

Revision date: 15/02/2017

Revision No: 7

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: SAPPHIRE AQUA 2

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Lubricating Grease

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Eye Irrit. 2: H319; Aquatic Chronic 3: H412; -: EUH208

Most important adverse effects: Contains amine phosphate. May produce an allergic reaction. Causes serious eye irritation.
Harmful to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: EUH208: Contains amine phosphate. May produce an allergic reaction.

H319: Causes serious eye irritation.

H412: Harmful to aquatic life with long lasting effects.

Hazard pictograms: GHS07: Exclamation mark



Signal words: Warning

Precautionary statements: P264: Wash hands thoroughly after handling.

[cont...]

SAFETY DATA SHEET

SAPPHIRE AQUA 2

Page: 2

P273: Avoid release to the environment.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P337+313: If eye irritation persists: Get medical attention.

P501: Dispose of contents/container to hazardous or special waste collection point.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

HYDROTREATED MINERAL OIL (LESS THAN 3% DMSO EXTRACT)

EINECS	CAS	PBT / WEL	CLP Classification	Percent
265-155-0	64742-52-5	Substance with a Community workplace exposure limit.	-	70-90%

ZINC O,O-BIS(ISOBUTYL/PENTYL)DITHIOPHOSPHATE

270-608-0	68457-79-4	-	Skin Irrit. 2: H315; Eye Dam. 1: H318; Aquatic Chronic 2: H411	1-2.4%
-----------	------------	---	--	--------

2,6-DI-TERT-BUTYL-P-CRESOL

204-881-4	128-37-0	-	Aquatic Acute 1: H400; Aquatic Chronic 1: H410	<1%
-----------	----------	---	--	-----

(Z)-N-9-OCTADECENYLPROPANE-1,3-DIAMINE

230-528-9	7173-62-8	-	Met. Corr. 1: H290; Acute Tox. 4: H302; Skin Corr. 1B: H314; Eye Dam. 1: H318; STOT RE 1: H372; Aquatic Acute 1: H400; Aquatic Chronic 1: H410	<1%
-----------	-----------	---	--	-----

AMINE PHOSPHATE

931-384-6	-	-	Eye Dam. 1: H318; Skin Sens. 1: H317; Aquatic Chronic 2: H411; Acute Tox. 4: H302	<1%
-----------	---	---	---	-----

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

[cont...]

SAFETY DATA SHEET

SAPPHIRE AQUA 2

Page: 3

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Alcohol resistant foam. Carbon dioxide. Dry chemical powder. Water fog.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS. Refer to section 13 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Must only be kept in original packaging.

[cont...]

SAFETY DATA SHEET

SAPPHIRE AQUA 2

Page: 4

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

HYDROTREATED MINERAL OIL (LESS THAN 3% DMSO EXTRACT)

Workplace exposure limits:

Respirable dust

State	8 hour TWA		15 min. STEL	
	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	5mg/m ³	-	-	-

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Respiratory protection not required.

Hand protection: Protective gloves. Nitrile gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Environmental: No special requirement.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Paste

Colour: Brown

Odour: Odourless

Evaporation rate: Negligible

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Insoluble

Viscosity: Highly viscous

Boiling point/range°C: No data available.

Melting point/range°C: > 150

Flammability limits %: lower: No data available.

upper: No data available.

Flash point°C: > 200

Part.coeff. n-octanol/water: No data available.

Autoflammability°C: > 200

Vapour pressure: No data available.

Relative density: < 1

pH: No data available.

VOC g/l: No data available.

[cont...]

SAFETY DATA SHEET

SAPPHIRE AQUA 2

Page: 5

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Relevant hazards for product:

Hazard	Route	Basis
Serious eye damage/irritation	OPT	Hazardous: calculated

Excluded hazards for substance:

Hazard	Route	Basis
Acute toxicity (ac. tox. 4)	-	No hazard: calculated
Acute toxicity (ac. tox. 3)	-	No hazard: calculated
Acute toxicity (ac. tox. 2)	-	No hazard: calculated
Acute toxicity (ac. tox. 1)	-	No hazard: calculated
Skin corrosion/irritation	-	No hazard: calculated
Respiratory/skin sensitisation	-	No hazard: calculated
Germ cell mutagenicity	-	No hazard: calculated
Carcinogenicity	-	No hazard: calculated

[cont...]

SAFETY DATA SHEET

SAPPHIRE AQUA 2

Page: 6

Reproductive toxicity	-	No hazard: calculated
STOT-single exposure	-	No hazard: calculated
STOT-repeated exposure	-	No hazard: calculated
Aspiration hazard	-	No hazard: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: No data available.

12.3. Bioaccumulative potential

Bioaccumulative potential: No data available.

12.4. Mobility in soil

Mobility: No data available.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: No data available.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Recovery operations: No data available

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

[cont...]

SAFETY DATA SHEET

SAPPHIRE AQUA 2

Page: 7

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: No data available

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

Compiled in accordance with REACH.

Phrases used in s.2 and s.3: EUH208: Contains <name of sensitising substance>. May produce an allergic reaction.

H290: May be corrosive to metals.

H302: Harmful if swallowed.

H314: Causes severe skin burns and eye damage.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H318: Causes serious eye damage.

H319: Causes serious eye irritation.

H372: Causes damage to organs <or state all organs affected, if known> through prolonged or repeated exposure <state route of exposure if it is conclusively proven that no other routes of exposure cause the hazard>.

H400: Very toxic to aquatic life.

H410: Very toxic to aquatic life with long lasting effects.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.