


62 12 120

Electronics Oblique Cutting Nipper



- With cutting edges for soft and medium hard wire
- Without bevel, for flush cutting
- Cutting edges additionally induction hardened, cutting edge hardness approx. 58 HRC
- Low-friction double spring for gentle and even opening
- Sturdy, zero backlash box joint
- The polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- High-grade special tool steel, forged, multi stage oil-hardened

Article No.	62 12 120
EAN	4003773017745
Head	polished
Handles	with multi-component grips
Cutting capacities medium hard wire (diameter) Ø mm	0,7
Cutting capacities soft wire (diameter) Ø mm	0,3 - 1,0
B mm	10
D mm	7,5
C mm	17
A mm	11
Dimensions angle °	15
Length mm	120
Net weight g	93



technical change and errors excepted

