


sensor box SRBE-CA3-YR90-R-2A-1W-C2N12-EX

Part number: 3471020

FESTO

For electrical feedback and position monitoring of process valves which are actuated with pneumatic quarter turn actuators, magnetic reed measuring principle.



Data sheet

Feature	Value
Design	Angular
Based on the standard	EN 60947-5-2 ISO 5211 VDI/VDE 3845
CE mark (see declaration of conformity)	to EU directive explosion protection (ATEX) to EU directive low-voltage devices
ATEX category Gas	II 2G
Explosion ignition protection type Gas	Ex d IIC T6 Gb
ATEX category Dust	II 2D
Explosion ignition protection type Dust	Ex tb IIIC T61°C Db
Explosion protection certification outside the EU	EPL Db (BR) EPL Db (CN) EPL Db (IEC-EX) EPL Gb (BR) EPL Gb (CN) EPL Gb (IEC-EX)
Explosion-proof ambient temperature	-20°C ≤ Ta ≤ +60°C
Certificate issuing department	DNV 16.0067X FTZU 15 ATEX 0095X GYJ 16.1497X IECEx FTZU 15.0014X
Materials note	Contains PWIS substances Conforms to RoHS
Safety Integrity Level (SIL)	SIL 2
Measuring principle	Reed magnetic
Ambient temperature	-20 ... 60 °C
Switch output	Contact-type
Switching element function	Toggle switch, single pole
Max. output current AC	0,416 A
Max. output current DC	3 A
Operating voltage range AC	0 ... 240 V
Operating voltage range DC	0 ... 30 V
Electrical connection	Screwed terminal 10-pin
Cable gland connection	NPT1/2
Connectable nominal conductor cross section	0,25 ... 2,5 mm ²
Mounting type	On flange to ISO 5211 With mounting bracket
Assembly position	Any
Product weight	1.700 g
Housing colour	silver
Materials information, housing	Aluminium die cast
Materials information for seals	NBR

Feature	Value
Materials information for shaft	High alloy steel, non-corrosive
Screw material data	High alloy steel, non-corrosive
Material information, mounting bracket	High alloy steel, non-corrosive
Material information, indicator	PC
Materials - Snap ring	High alloy steel, non-corrosive
Material information, disc	High alloy steel, non-corrosive
Position indicator	Yellow/red
Setting range, angle recording	0 ... 90 deg
Storage temperature	-20 ... 60 °C
Protection class	IP65
Shock resistance	Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test at severity level 2 in accordance with FN 942017-4 and EN 60068-2-6
Degree of contamination	3