

## SAFETY DATA SHEET

### Aromatic Free Acrylic Gel

According to Regulation (EC) No 1907/2006, Annex II, as amended. Commission Regulation (EU) No 2015/830 of 28 May 2015.

#### SECTION 1: Identification of the substance/mixture and of the company/undertaking

##### 1.1. Product identifier

Product name Aromatic Free Acrylic Gel

Product number AFAG, EAFAG35SL, ZE

##### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Appliance protection.

Uses advised against No specific uses advised against are identified.

##### 1.3. Details of the supplier of the safety data sheet

Supplier ELECTROLUBE. A division of HK WENTWORTH LTD  
ASHBY PARK, COALFIELD WAY,  
ASHBY DE LA ZOUCH, LEICESTERSHIRE LE65 1JR  
UNITED KINGDOM  
+44 (0)1530 419600  
+44 (0)1530 416640  
info@hkw.co.uk

##### 1.4. Emergency telephone number

Emergency telephone IN CASE OF EMERGENCY CALL:  
+44 1865 407333 (24hr, Provided by Carechem 24)  
+353 (0)1 809 2166 (Beaumont Hospital, Republic of Ireland only, 8am-10pm, 7 days a week)

#### SECTION 2: Hazards identification

##### 2.1. Classification of the substance or mixture

###### Classification (EC 1272/2008)

Physical hazards Flam. Liq. 3 - H226

Health hazards STOT SE 3 - H336

Environmental hazards Not Classified

##### 2.2. Label elements

###### Pictogram



Signal word Warning

Hazard statements H226 Flammable liquid and vapour.  
H336 May cause drowsiness or dizziness.

## Aromatic Free Acrylic Gel

**Precautionary statements**

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P261 Avoid breathing vapour/ spray.

P312 Call a POISON CENTRE/doctor if you feel unwell.

P370+P378 In case of fire: Use foam, carbon dioxide, dry powder or water fog to extinguish.

P403+P233 Store in a well-ventilated place. Keep container tightly closed.

P501 Dispose of contents/ container in accordance with national regulations.

**Contains** n-Butyl acetate

**Supplementary precautionary statements**

P240 Ground and bond container and receiving equipment.

P241 Use explosion-proof electrical equipment.

P242 Use non-sparking tools.

P243 Take action to prevent static discharges.

P271 Use only outdoors or in a well-ventilated area.

P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.

P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower.

P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P403+P235 Store in a well-ventilated place. Keep cool.

### 2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

## SECTION 3: Composition/information on ingredients

### 3.2. Mixtures

<b>n-Butyl acetate</b>	<b>30-60%</b>
CAS number: 123-86-4	EC number: 204-658-1
	REACH registration number: 01-2119485493-29-XXXX
<b>Classification</b>	
Flam. Liq. 3 - H226	
STOT SE 3 - H336	

The full text for all hazard statements is displayed in Section 16.

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

**General information** If in doubt, get medical attention promptly. Show this Safety Data Sheet to the medical personnel.

**Inhalation** Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Loosen tight clothing such as collar, tie or belt. Get medical attention if symptoms are severe or persist.

**Ingestion** Rinse mouth thoroughly with water. Get medical advice/attention if you feel unwell. Do not induce vomiting unless under the direction of medical personnel.

**Skin contact** Rinse with water.

**Eye contact** Remove any contact lenses and open eyelids wide apart. Rinse with water. Get medical attention if any discomfort continues.

**Protection of first aiders** First aid personnel should wear appropriate protective equipment during any rescue.

### 4.2. Most important symptoms and effects, both acute and delayed

## Aromatic Free Acrylic Gel

<b>General information</b>	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
<b>Inhalation</b>	No specific symptoms known.
<b>Ingestion</b>	No specific symptoms known.
<b>Skin contact</b>	No specific symptoms known.
<b>Eye contact</b>	No specific symptoms known. May be slightly irritating to eyes.

### 4.3. Indication of any immediate medical attention and special treatment needed

**Notes for the doctor** Treat symptomatically.

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

**Suitable extinguishing media** The product is flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.

**Unsuitable extinguishing media** Do not use water jet as an extinguisher, as this will spread the fire.

### 5.2. Special hazards arising from the substance or mixture

**Specific hazards** Containers can burst violently or explode when heated, due to excessive pressure build-up. Flammable liquid and vapour. Vapours may be ignited by a spark, a hot surface or an ember. Vapours may form explosive mixtures with air. Fire-water run-off in sewers may create fire or explosion hazard.

**Hazardous combustion products** Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

### 5.3. Advice for firefighters

**Protective actions during firefighting** Avoid breathing fire gases or vapours. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapours and protect men stopping the leak. Control run-off water by containing and keeping it out of sewers and watercourses. If risk of water pollution occurs, notify appropriate authorities.

**Special protective equipment for firefighters** Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Firefighter's clothing conforming to European standard EN469 (including helmets, protective boots and gloves) will provide a basic level of protection for chemical incidents.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions** Wear protective clothing as described in Section 8 of this safety data sheet. No action shall be taken without appropriate training or involving any personal risk. Do not touch or walk into spilled material. Evacuate area. Provide adequate ventilation. No smoking, sparks, flames or other sources of ignition near spillage. Promptly remove any clothing that becomes contaminated.

### 6.2. Environmental precautions

**Environmental precautions** Avoid discharge into drains or watercourses or onto the ground.

### 6.3. Methods and material for containment and cleaning up

## Aromatic Free Acrylic Gel

### Methods for cleaning up

Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Eliminate all ignition sources if safe to do so. No smoking, sparks, flames or other sources of ignition near spillage. Do not allow material to enter confined spaces, due to the risk of explosion. Absorb small quantities with paper towels and evaporate in a safe place. Once evaporation is complete, place paper in a suitable waste disposal container and seal securely. Large Spillages: If the product is soluble in water, dilute the spillage with water and mop it up. Alternatively, or if it is not water-soluble, absorb the spillage with an inert, dry material and place it in a suitable waste disposal container. The contaminated absorbent may pose the same hazard as the spilled material. Label the containers containing waste and contaminated materials and remove from the area as soon as possible. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. For waste disposal, see Section 13.

### 6.4. Reference to other sections

**Reference to other sections** For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

#### Usage precautions

Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimise spills. Keep container tightly sealed when not in use. Avoid the formation of mists. The product is flammable. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not handle until all safety precautions have been read and understood. Do not handle broken packages without protective equipment. Do not reuse empty containers.

#### Advice on general occupational hygiene

Wash promptly if skin becomes contaminated. Take off contaminated clothing. Wash contaminated clothing before reuse.

### 7.2. Conditions for safe storage, including any incompatibilities

#### Storage precautions

Store away from incompatible materials (see Section 10). Keep away from oxidising materials, heat and flames. Keep only in the original container. Keep container tightly closed, in a cool, well ventilated place. Keep containers upright. Protect containers from damage.

#### Storage class

Flammable liquid storage.

### 7.3. Specific end use(s)

#### Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

## SECTION 8: Exposure controls/Personal protection

### 8.1. Control parameters

#### Occupational exposure limits

##### n-Butyl acetate

Long-term exposure limit (8-hour TWA): WEL 150 ppm 724 mg/m<sup>3</sup>

Short-term exposure limit (15-minute): WEL 200 ppm 966 mg/m<sup>3</sup>

WEL = Workplace Exposure Limit

### 8.2. Exposure controls

## Aromatic Free Acrylic Gel

### Protective equipment



### Appropriate engineering controls

Provide adequate ventilation. Observe any occupational exposure limits for the product or ingredients.

### Eye/face protection

Unless the assessment indicates a higher degree of protection is required, the following protection should be worn: Tight-fitting safety glasses.

### Hand protection

No specific hand protection recommended.

### Other skin and body protection

Wear appropriate clothing to prevent repeated or prolonged skin contact.

### Hygiene measures

Wash after use and before eating, smoking and using the toilet. Do not eat, drink or smoke when using this product.

### Respiratory protection

Ensure all respiratory protective equipment is suitable for its intended use and is 'CE'-marked. Check that the respirator fits tightly and the filter is changed regularly. Gas and combination filter cartridges should comply with European Standard EN14387. Full face mask respirators with replaceable filter cartridges should comply with European Standard EN136. Half mask and quarter mask respirators with replaceable filter cartridges should comply with European Standard EN140.

### Environmental exposure controls

Keep container tightly sealed when not in use.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Appearance	Gel.
Colour	Light (or pale).
Odour	Organic solvents.
Odour threshold	Not available.
pH	Not available.
Melting point	Not available.
Initial boiling point and range	Not available.
Flash point	28.5°C Closed cup.
Evaporation rate	Not available.
Evaporation factor	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	Not available.
Other flammability	Not available.
Vapour pressure	Not available.
Vapour density	Not available.
Relative density	Not available.

## Aromatic Free Acrylic Gel

<b>Bulk density</b>	Not available.
<b>Solubility(ies)</b>	Not available.
<b>Partition coefficient</b>	Not available.
<b>Auto-ignition temperature</b>	Not available.
<b>Decomposition Temperature</b>	Not available.
<b>Viscosity</b>	6000 mPa s @ 20°C/68°F
<b>Explosive properties</b>	Not considered to be explosive.
<b>Oxidising properties</b>	Does not meet the criteria for classification as oxidising.

### 9.2. Other information

#### SECTION 10: Stability and reactivity

##### 10.1. Reactivity

**Reactivity** See the other subsections of this section for further details.

##### 10.2. Chemical stability

**Stability** Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.

##### 10.3. Possibility of hazardous reactions

**Possibility of hazardous reactions** The following materials may react strongly with the product: Oxidising agents.

##### 10.4. Conditions to avoid

**Conditions to avoid** Avoid heat, flames and other sources of ignition. Containers can burst violently or explode when heated, due to excessive pressure build-up. Static electricity and formation of sparks must be prevented.

##### 10.5. Incompatible materials

**Materials to avoid** Oxidising materials. Acids - oxidising.

##### 10.6. Hazardous decomposition products

**Hazardous decomposition products** Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.

#### SECTION 11: Toxicological information

##### 11.1. Information on toxicological effects

###### Acute toxicity - oral

**Notes (oral LD<sub>50</sub>)** Based on available data the classification criteria are not met.

###### Acute toxicity - dermal

**Notes (dermal LD<sub>50</sub>)** Based on available data the classification criteria are not met.

###### Acute toxicity - inhalation

**Notes (inhalation LC<sub>50</sub>)** Based on available data the classification criteria are not met.

###### Skin corrosion/irritation

**Animal data** Based on available data the classification criteria are not met.

###### Serious eye damage/irritation

**Serious eye damage/irritation** Based on available data the classification criteria are not met.

## Aromatic Free Acrylic Gel

### Respiratory sensitisation

**Respiratory sensitisation** Based on available data the classification criteria are not met.

### Skin sensitisation

**Skin sensitisation** Based on available data the classification criteria are not met.

### Germ cell mutagenicity

**Genotoxicity - in vitro** Based on available data the classification criteria are not met.

### Carcinogenicity

**Carcinogenicity** Based on available data the classification criteria are not met.

### IARC carcinogenicity

None of the ingredients are listed or exempt.

### Reproductive toxicity

**Reproductive toxicity - fertility** Based on available data the classification criteria are not met.

### Reproductive toxicity - development

Based on available data the classification criteria are not met.

### Specific target organ toxicity - single exposure

**STOT - single exposure** Not classified as a specific target organ toxicant after a single exposure.

### Specific target organ toxicity - repeated exposure

**STOT - repeated exposure** Not classified as a specific target organ toxicant after repeated exposure.

### Aspiration hazard

**Aspiration hazard** Based on available data the classification criteria are not met.

### General information

The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

### Inhalation

No specific symptoms known.

### Ingestion

No specific symptoms known.

### Skin contact

No specific symptoms known.

### Eye contact

No specific symptoms known.

### Route of exposure

Ingestion Inhalation Skin and/or eye contact

### Target organs

No specific target organs known.

### Toxicological information on ingredients.

#### n-Butyl acetate

#### Acute toxicity - oral

**Acute toxicity oral (LD<sub>50</sub> mg/kg)** 10,760.0

**Species** Rat

**ATE oral (mg/kg)** 10,760.0

#### Acute toxicity - inhalation

**Acute toxicity inhalation (LC<sub>50</sub> vapours mg/l)** 23.4

**Species** Rat

## Aromatic Free Acrylic Gel

ATE inhalation (vapours mg/l) 23.4

### 2,5-thiophenediylbis(5-tert-butyl-1,3-benzoxazole)

#### Acute toxicity - oral

Acute toxicity oral (LD<sub>50</sub> mg/kg) 10,000.0

Species Rat

ATE oral (mg/kg) 10,000.0

### SECTION 12: Ecological information

**Ecotoxicity** Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.

#### 12.1. Toxicity

**Toxicity** Based on available data the classification criteria are not met.

#### 12.2. Persistence and degradability

**Persistence and degradability** The degradability of the product is not known.

#### 12.3. Bioaccumulative potential

**Bioaccumulative potential** No data available on bioaccumulation.

**Partition coefficient** Not available.

#### 12.4. Mobility in soil

**Mobility** No data available.

#### 12.5. Results of PBT and vPvB assessment

#### 12.6. Other adverse effects

**Other adverse effects** None known.

### SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

**General information** The generation of waste should be minimised or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. When handling waste, the safety precautions applying to handling of the product should be considered. Care should be taken when handling emptied containers that have not been thoroughly cleaned or rinsed out. Empty containers or liners may retain some product residues and hence be potentially hazardous.

**Disposal methods** Do not empty into drains. Dispose of surplus products and those that cannot be recycled via a licensed waste disposal contractor. Waste, residues, empty containers, discarded work clothes and contaminated cleaning materials should be collected in designated containers, labelled with their contents. Incineration or landfill should only be considered when recycling is not feasible.

### SECTION 14: Transport information

**General** For limited quantity packaging/limited load information, consult the relevant modal documentation using the data shown in this section.

#### 14.1. UN number



## Aromatic Free Acrylic Gel

UN No. (ADR/RID)	1263
UN No. (IMDG)	1263
UN No. (ICAO)	1263
UN No. (ADN)	1263

### 14.2. UN proper shipping name

Proper shipping name (ADR/RID)	PAINT
Proper shipping name (IMDG)	PAINT
Proper shipping name (ICAO)	PAINT
Proper shipping name (ADN)	PAINT

### 14.3. Transport hazard class(es)

ADR/RID class	3
ADR/RID classification code	F1
ADR/RID label	3
IMDG class	3
ICAO class/division	3
ADN class	3

#### Transport labels



### 14.4. Packing group

ADR/RID packing group	III
IMDG packing group	III
ICAO packing group	III
ADN packing group	III

### 14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant  
No.

### 14.6. Special precautions for user

Always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

EmS	F-E, S-E
ADR transport category	3
Emergency Action Code	•3Y
Hazard Identification Number (ADR/RID)	30
Tunnel restriction code	(D/E)

## Aromatic Free Acrylic Gel

### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

<b>National regulations</b>	Health and Safety at Work etc. Act 1974 (as amended). The Carriage of Dangerous Goods and Use of Transportable Pressure Equipment Regulations 2009 (SI 2009 No. 1348) (as amended) ["CDG 2009"]. EH40/2005 Workplace exposure limits.
<b>EU legislation</b>	Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended). Commission Regulation (EU) No 2015/830 of 28 May 2015. Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).

#### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

#### Inventories

##### **EU - EINECS/ELINCS**

None of the ingredients are listed or exempt.

### SECTION 16: Other information

<b>Abbreviations and acronyms used in the safety data sheet</b>	ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road. ADN: European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways. RID: European Agreement concerning the International Carriage of Dangerous Goods by Rail. IATA: International Air Transport Association. ICAO: Technical Instructions for the Safe Transport of Dangerous Goods by Air. IMDG: International Maritime Dangerous Goods. CAS: Chemical Abstracts Service. ATE: Acute Toxicity Estimate. LC <sub>50</sub> : Lethal Concentration to 50 % of a test population. LD <sub>50</sub> : Lethal Dose to 50% of a test population (Median Lethal Dose). EC <sub>50</sub> : 50% of maximal Effective Concentration. PBT: Persistent, Bioaccumulative and Toxic substance. vPvB: Very Persistent and Very Bioaccumulative.
<b>Classification abbreviations and acronyms</b>	Flam. Liq. = Flammable liquid
<b>Classification procedures according to Regulation (EC) 1272/2008</b>	Flam. Liq. 3 - H226: : Expert judgement.
<b>Training advice</b>	Only trained personnel should use this material.
<b>Issued by</b>	Bethan Massey

## Aromatic Free Acrylic Gel

<b>Revision date</b>	22/08/2018
<b>Revision</b>	1
<b>SDS number</b>	1273
<b>Hazard statements in full</b>	H226 Flammable liquid and vapour. H336 May cause drowsiness or dizziness.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.