



PEG124, Aluminum Electrolytic, 15 uF, -10/+30%, 450 VDC, -40/+105°C



Dimensions	
D	16mm +/-0.5mm
L	37mm +/-1mm
L1	43mm MIN
LL Negative	42mm +3/-2mm
LL Positive	42mm +3/-2mm
F	0.8mm +/-0.03mm

Packaging Specifications	
Weight:	11 g
Packaging:	Bulk, Bag
Packaging Quantity:	100

General Information	
Supplier:	KEMET
Series:	PEG124
Dielectric:	Aluminum Electrolytic
Style:	Axial
Description:	Long Life Axial Aluminum Electrolytic
Features:	Long Life
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	No
Miscellaneous:	Life Calculation Based On Maximum Ripple Current, Please Contact KEMET For More Information
Notes:	L1 is KEMETs recommendation for minimum distance between symmetrical Lead bend. Available only for Customer specific part numbers. Lead bend dimensions must be specified and confirmed per article.
Shelf Life:	156 Weeks

Specifications	
Capacitance:	15 uF
Capacitance Tolerance:	-10/+30%
Voltage DC:	450 VDC
Temperature Range:	-40/+105°C
Rated Temperature:	105°C
Life:	15000 Hrs
Resistance:	3600 mOhms (100Hz 20C), 1700 mOhms (100kHz 20C)
Ripple Current:	0.171 Amps (100Hz 125C), 1.1 Amps (5kHz 60C), 0.41 Amps (5kHz 125C)
Leakage Current:	20 uA (5min 20°C)
Inductance:	12 nH (ESL)